


| REVISIONS |     |               |         |     |      |
|-----------|-----|---------------|---------|-----|------|
| P         | LTR | DESCRIPTION   | DATE    | OWN | APVD |
|           | A   | ECO-16-009990 | 06JUL16 | KG  | SM   |

1. MAXIMUM INSERTION LOSS IS 0.4dB AT 850nm.

△2 SEE TRACE LABEL DETAIL.

3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE SPEC TEC-138-702.



XXXXXXXXXXXXXXXXX

1918412-X

TRACE NO.

TE P/N

△2 TRACE LABEL DETAIL  
(NOT TO SCALE)

|                                  |             |
|----------------------------------|-------------|
| 0.610±0.013 [24.0±0.5]           | 1918412-5   |
| 0.305±0.013 [12.0±0.5]           | 1918412-4   |
| 1.100+0.020/-0.0 [43.3+0.8/-0.0] | 1918412-3   |
| 0.400+0.020/-0.0 [15.7+0.8/-0.0] | 1918412-2   |
| 3.810±0.080 [150.0±3.1]          | 1918412-1   |
| L METERS [INCHES]                | PART NUMBER |

|                                        |                                                                                       |                             |                                                                                            |                       |                 |
|----------------------------------------|---------------------------------------------------------------------------------------|-----------------------------|--------------------------------------------------------------------------------------------|-----------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |                                                                                       | DWN<br>J.W.DAVIS<br>14MAR06 | TE Connectivity                                                                            |                       |                 |
| DIMENSIONS:<br>METERS [INCHES]         |                                                                                       | CHK<br>J.BARRY<br>14MAR06   |                                                                                            |                       |                 |
|                                        | TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                |                             | NAME<br>CABLE ASSEMBLY, FO, 2.0mm SIMPLEX<br>62.5/125um CABLE ARINC 801 MT TO ARINC 801 MT |                       |                 |
|                                        | 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± -<br>FINISH |                             | APVD<br>J.BARRY<br>14MAR06                                                                 |                       |                 |
|                                        | MATERIAL                                                                              |                             | PRODUCT SPEC                                                                               |                       |                 |
|                                        |                                                                                       | WEIGHT<br>0                 | APPLICATION SPEC                                                                           |                       |                 |
|                                        |                                                                                       | CUSTOMER DRAWING            |                                                                                            | SIZE<br>A2            | RESTRICTED TO   |
|                                        |                                                                                       |                             |                                                                                            | CAGE CODE<br>00779    | REV             |
|                                        |                                                                                       |                             |                                                                                            | DRAWING NO<br>1918412 | A               |
|                                        |                                                                                       |                             |                                                                                            | SCALE<br>NTS          | SHEET<br>1 OF 1 |