



| LOC | DIST | REVISIONS |     |                           |  |         |      |
|-----|------|-----------|-----|---------------------------|--|---------|------|
|     |      | P         | LTR | DESCRIPTION               |  | DATE    | APVD |
| EH  | 00   |           | D1  | REVISED PER ECO-11-005033 |  | 22MAR11 | HMR  |



1. ONE CABLE PACKAGED IN A POLY BAG.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. CABLE: SHIELDED 26 AWG, 4 TWISTED PAIRS, 7/34 STRANDED CONDUCTORS, 100 OHMS CAT6A.
4. DESIGNATIONS IN PARENTHESES ( ) ARE FOR REFERENCE ONLY.



|             |           |                   |             |             |           |                 |             |
|-------------|-----------|-------------------|-------------|-------------|-----------|-----------------|-------------|
| 30.48       | 100       | 30632.4 (1206.00) | 9-1933881-9 | 8.53        | 28        | 8686.8 (342.00) | 2-1933881-8 |
| 0.15        | 0.5       | 203.2 (8.00)      | 9-1933881-8 | 7.92        | 26        | 8077.2 (318.00) | 2-1933881-6 |
| 28.96       | 95        | 29108.4 (1146.00) | 9-1933881-5 | 7.32        | 24        | 7416.8 (292.00) | 2-1933881-4 |
| 27.43       | 90        | 27584.4 (1086.00) | 9-1933881-0 | 6.71        | 22        | 6807.2 (268.00) | 2-1933881-2 |
| 25.91       | 85        | 26060.4 (1026.00) | 8-1933881-5 | 6.1         | 20        | 6197.6 (244.00) | 2-1933881-0 |
| 24.38       | 80        | 24536.4 (966.00)  | 8-1933881-0 | 5.49        | 18        | 5588.0 (220.00) | 1-1933881-8 |
| 22.86       | 75        | 23012.4 (906.00)  | 7-1933881-5 | 4.88        | 16        | 4978.4 (196.00) | 1-1933881-6 |
| 21.34       | 70        | 21488.4 (846.00)  | 7-1933881-0 | 4.57        | 15        | 4673.6 (184.00) | 1-1933881-5 |
| 19.81       | 65        | 19964.4 (786.00)  | 6-1933881-5 | 4.27        | 14        | 4368.8 (172.00) | 1-1933881-4 |
| 18.29       | 60        | 18440.4 (726.00)  | 6-1933881-0 | 3.66        | 12        | 3759.2 (148.00) | 1-1933881-2 |
| 16.76       | 55        | 16916.4 (666.00)  | 5-1933881-5 | 3.05        | 10        | 3149.6 (124.00) | 1-1933881-0 |
| 15.24       | 50        | 15392.4 (606.00)  | 5-1933881-0 | 2.74        | 9         | 2794.0 (110.00) | 1933881-9   |
| 13.72       | 45        | 13868.4 (546.00)  | 4-1933881-5 | 2.44        | 8         | 2489.2 (98.00)  | 1933881-8   |
| 12.20       | 40        | 12344.4 (486.00)  | 4-1933881-0 | 2.14        | 7         | 2184.4 (86.00)  | 1933881-7   |
| 11.58       | 38        | 11734.8 (462.00)  | 3-1933881-8 | 1.83        | 6         | 1879.6 (74.00)  | 1933881-6   |
| 10.97       | 36        | 11125.2 (438.00)  | 3-1933881-6 | 1.53        | 5         | 1574.8 (62.00)  | 1933881-5   |
| 10.36       | 34        | 10515.6 (414.00)  | 3-1933881-4 | 1.22        | 4         | 1270.0 (50.00)  | 1933881-4   |
| 9.75        | 32        | 9906.0 (390.00)   | 3-1933881-2 | 0.92        | 3         | 965.2 (38.00)   | 1933881-3   |
| 9.14        | 30        | 9296.4 (366.00)   | 3-1933881-0 | 0.61        | 2         | 660.4 (26.00)   | 1933881-2   |
|             |           |                   |             | 0.30        | 1         | 355.6 (14.00)   | 1933881-1   |
| METERS, REF | FEET, REF | DIM A             | PART NO     | METERS, REF | FEET, REF | DIM A           | PART NO     |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

MATERIAL  
- 3

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |     |
|--------|-----|
| 0 PLC  | ± - |
| 1 PLC  | ± - |
| 2 PLC  | ± - |
| 3 PLC  | ± - |
| 4 PLC  | ± - |
| ANGLES | ± - |
| FINISH | -   |

DWN  
L. HALL  
13OCT2008

CHK  
J. GENIAC  
17OCT2008

APVD  
J. GENIAC  
17OCT2008

PRODUCT SPEC  
-

APPLICATION SPEC  
-

WEIGHT  
-

CUSTOMER DRAWING

TE Connectivity

CABLE ASSY, MOD PLUG, 8 POSN, SHIELDED, GRAY, CAT 6A

|              |                    |                         |                    |
|--------------|--------------------|-------------------------|--------------------|
| SIZE<br>A2   | CAGE CODE<br>00779 | DRAWING NO<br>C=1933881 | RESTRICTED TO<br>- |
| SCALE<br>NTS | SHEET<br>1 OF 1    | REV<br>D1               |                    |