


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C4	REVISED PER ECO-14-009081	02JUL2014	NK	MM



1 HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 WIRE SIZE RANGE:
12 - 30 AWG






3 NOT CUMULATIVE TOLERANCE.


4 PRELIMINARY

5 SPECIAL MARKING TO BE PERMANENT BLACK LETTERING

6 SPECIAL MARKING TO BE IN PERMANENT BLACK INK

7 SPECIAL MARKING TO BE PERMANENT WHITE INK (SEE BACKGROUND)



	DETAIL D	20.32	4	2-284041-9
	DETAIL C	20.32	4	2-284041-8
	DETAIL B	20.32	4	2-284041-7
	DETAIL A	20.32	4	2-284041-6
		127.00	25	2-284041-5
		121.92	24	2-284041-4
		116.84	23	2-284041-3
		111.76	22	2-284041-2
		106.68	21	2-284041-1
		101.60	20	2-284041-0
		96.52	19	1-284041-9
		91.44	18	1-284041-8
		86.36	17	1-284041-7
		81.28	16	1-284041-6
		76.20	15	1-284041-5
		71.12	14	1-284041-4
		66.04	13	1-284041-3
		60.96	12	1-284041-2
		55.88	11	1-284041-1
		50.80	10	1-284041-0
		45.72	9	284041-9
		40.64	8	284041-8
		35.56	7	284041-7
		30.48	6	284041-6
		25.40	5	284041-5
	20.32	4	284041-4	
	15.24	3	284041-3	
	10.16	2	284041-2	
	DIM. A	NO OF POS.	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN E. ZANOLIN 27MAR2001		 TE Connectivity		DWM: X		REV: C		PART NUMBER						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK D. BIEVENOUR 27MAR2001													
		0 PLC ±0.3		NAME TERMINAL BLOCK, VERTICAL PLUG STACKING, LEFT HAND 5.08mm PITCH		APVD D. BIEVENOUR 27MAR2001		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		1 PLC ±0.25															
		2 PLC ±0.25															
		3 PLC ±0.25		APPLICATION SPEC		-		A2		b0779		C-284041		-			
		4 PLC ±0.25															
		ANGLES ±2															
MATERIAL		FINISH		WEIGHT		-		A2		b0779		C-284041		-			
				-		CUSTOMER DRAWING		SCALE		4.1		SHEET		OF		REV	
																C4	