



|     |      |           |     |                   |         |     |      |
|-----|------|-----------|-----|-------------------|---------|-----|------|
|     |      | 1         |     |                   |         |     |      |
| LOC | DIST | REVISIONS |     |                   |         |     |      |
| EH  | 00   | P         | LTR | DESCRIPTION       | DATE    | DWN | APVD |
|     |      |           | D1  | ECO-06-010649     | 01AUG06 | JM  | CC   |
|     |      |           | D2  | REV ECO-06-023840 | 11OCT06 | LH  | CC   |
|     |      |           | E   | REV ECO-06-27719  | 05JAN07 | LH  | CD   |



- ONE CABLE PACKAGED IN A CLEAR POLYBAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: UNSHIELDED 24 AWG, 4 TWISTED PAIRS, 7/32 STRANDED CONDUCTORS, 100 OHMS.
- DESIGNATIONS IN PARENTHESES ( ) ARE FOR REFERENCE ONLY.
- AN ALTERNATE FORM OF CONNECTOR COMPONENTS RESULTING IN EQUIVALENT PERFORMANCE IS ACCEPTABLE.



|       |     |                   |            |
|-------|-----|-------------------|------------|
| 30.48 | 100 | 30632.4 (1206.00) | 9-219241-9 |
| 0.15  | 0.5 | 203.2 (8.00)      | 9-219241-8 |
| 27.74 | 91  | 27889.2 (1098.00) | 9-219241-1 |
| 18.29 | 60  | 18440.4 (726.00)  | 6-219241-0 |
| 15.24 | 50  | 15392.4 (606.00)  | 5-219241-0 |
| 12.20 | 40  | 12344.4 (486.00)  | 4-219241-0 |
| 9.15  | 30  | 9296.4 (366.00)   | 3-219241-0 |
| 7.62  | 25  | 7721.6 (304.00)   | 2-219241-5 |
| 6.10  | 20  | 6197.6 (244.00)   | 2-219241-0 |
| 4.88  | 16  | 4978.4 (196.00)   | 1-219241-6 |
| 4.57  | 15  | 4724.4 (184.00)   | 1-219241-5 |
| 4.27  | 14  | 4368.8 (172.00)   | 1-219241-4 |
| 3.66  | 12  | 3759.2 (148.00)   | 1-219241-2 |
| 3.05  | 10  | 3149.6 (124.00)   | 1-219241-0 |
| 2.74  | 9   | 2794.0 (110.00)   | 219241-9   |
| 2.44  | 8   | 2489.2 (98.00)    | 219241-8   |
| 2.14  | 7   | 2184.4 (86.00)    | 219241-7   |
| 1.83  | 6   | 1879.6 (74.00)    | 219241-6   |
| 1.53  | 5   | 1574.8 (62.00)    | 219241-5   |
| 1.22  | 4   | 1270.0 (50.00)    | 219241-4   |
| 0.92  | 3   | 965.2 (38.00)     | 219241-3   |
| 0.61  | 2   | 660.4 (26.00)     | 219241-2   |
| 0.30  | 1   | 355.6 (14.00)     | 219241-1   |

|                                        |           |                                                                |         |
|----------------------------------------|-----------|----------------------------------------------------------------|---------|
| METERS, REF                            | FEET, REF | DIM A                                                          | PART NO |
| THIS DRAWING IS A CONTROLLED DOCUMENT. |           |                                                                |         |
| DIMENSIONS: mm[INCHES]                 |           | TOLERANCES UNLESS OTHERWISE SPECIFIED:                         |         |
| 0 PLC ± -                              |           | 1 PLC ± -                                                      |         |
| 2 PLC ± -                              |           | 3 PLC ± -                                                      |         |
| 4 PLC ± -                              |           | ANGLES ± -                                                     |         |
| FINISH                                 |           | FINISH                                                         |         |
| MATERIAL                               |           | MATERIAL                                                       |         |
| - 3                                    |           | -                                                              |         |
| DWN M. BOLES 25JUL97                   |           | CHK B. ANTHONY 25JUL01                                         |         |
| APVD B. ANTHONY 25JUL97                |           | PRODUCT SPEC                                                   |         |
| 108-1163                               |           | APPLICATION SPEC                                               |         |
| 114-6053                               |           | WEIGHT                                                         |         |
| CUSTOMER DRAWING                       |           | SCALE NTS                                                      |         |
| SHEET 1 of 1                           |           | REV E                                                          |         |
| tyco Electronics                       |           | Tyco Electronics Corporation Harrisburg, PA 17105-3608         |         |
| NAME                                   |           | CABLE ASSEMBLY, MOD PLUG, 8 POSITION GRAY, ENHANCED CATEGORY 5 |         |
| SIZE                                   |           | CAGE CODE                                                      |         |
| A2                                     |           | 00779                                                          |         |
| DRAWING NO                             |           | RESTRICTED TO                                                  |         |
| C=219241                               |           | -                                                              |         |