

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		—	SEE SHEET 1	—	—	—

SELECT LOAD CHART

9,10	1-8	1-8	9,10	9,10	-	1-8	-	-	10	SSB7N2030	5-1546963-8
1-8	9,10	-	-	2,5,6,10	-	1,7	-	-	10	SSB7N2025	4-1546963-3
ALL	ALL	2,3,4	-	-	-	-	-	-	7	SSB7N2019	3-1546963-8
ALL	ALL	3,4	-	-	-	-	-	-	7	SSB7N2017	3-1546963-2
-	-	ALL	-	-	-	2,4	-	-	6	SSB7N2016	3-1546963-1
-	1,3,5,7	-	-	1	-	-	-	-	4	SSB7CG04032224	4-1546963-9
.250 QC TAB 90° BEND SGL SIDED	.250 QC TAB 90° BEND DBL SIDED	.250 QC TAB STRAIGHT DBL SIDED	.250 QC TAB STRAIGHT SGL SIDED	.250 QC TAB 45° BEND SGL SIDED	.187 QC TAB STRAIGHT SGL SIDED	.250 QC TAB 45° BEND DBL SIDED	.187 QC TAB 45° BEND SGL SIDED	.187 QC TAB 90° BEND SGL SIDED	NO. OF POS.	CATALOG NUMBER	PART NUMBER
⑩	⑨	⑧	⑦	⑥	⑤	④	③	②	POSITIONS LOADED		

3 4	1.750	2.312	—	2	—	—	2	—	—	—	2	—	—	YES	3	SSB7CG030328—SPL	6—1546963—3
	11.375	11.937	—	—	—	—	—	—	—	—	—	—	—	YES	25	SSB70G250301	2—1546963—5
	10.937	11.500	—	—	—	—	—	—	—	—	—	—	—	YES	24	SSB70G240301	2—1546963—4
	10.500	11.062	—	—	—	—	—	—	—	—	—	—	—	YES	23	SSB70G230301	2—1546963—3
	10.062	10.625	—	—	—	—	—	—	—	—	—	—	—	YES	22	SSB70G220304	6—1546963—1
	10.062	10.625	—	—	—	—	—	—	—	—	—	—	—	YES	22	SSB70G220301	2—1546963—2
	9.625	10.187	—	—	—	—	—	—	—	—	—	—	—	YES	21	SSB70G210301	2—1546963—1
	9.187	9.750	—	—	—	—	—	—	—	—	—	—	—	YES	20	SSB70G200301	2—1546963—0
4	8.750	9.312	—	—	—	—	—	—	—	—	—	—	—	YES	19	SSB7CG190301	1—1546963—9
	8.313	8.875	—	—	—	—	—	—	—	—	—	—	—	YES	18	SSB7CG180301	1—1546963—8
	7.875	8.437	—	—	—	—	—	—	—	—	—	—	—	YES	17	SSB7CG170301	1—1546963—7
	7.437	8.000	—	—	—	—	—	—	—	—	—	—	—	YES	16	SSB7CG160301	1—1546963—6
	7.000	7.562	—	—	—	—	—	—	—	—	—	—	—	YES	15	SSB7CG150301	1—1546963—5
	1 3 4	6.562	7.125	—	—	—	14	—	—	—	14	—	—	YES	14	SSB7N2020	3—1546963—4
		6.562	7.125	—	—	—	—	—	—	—	—	—	—	YES	14	SSB7CG140301	7—1437415—6
		6.125	6.687	—	—	—	—	—	—	—	—	—	—	YES	13	SSB7CG130301	1—1546963—3
5.687		6.250	—	—	—	—	—	—	—	—	—	—	YES	12	SSB7CG120301	1—1546963—2	
3		5.250	5.812	—	—	—	—	11	11	—	—	—	—	YES	11	SSB7CG110329	1—1546963—6
		5.250	5.812	—	—	—	—	—	—	—	—	—	—	YES	11	SSB7CG110301	1—1546963—1
3 4		4.812	5.375	—	—	2	8	8	2	2	—	8	—	YES	10	SSB7N2030	5—1546963—8
		4.812	5.375	—	—	2	8	—	—	4	—	2	—	NO	10	SSB7N2025	4—1546963—3
3 4	4.812	5.375	—	—	—	—	—	—	—	—	—	—	YES	10	SSB7CG100301	1—1546963—0	
	DIM B	DIM A	JUMPER	.250 QC TAB 90° BEND DBL SIDED ⑭	.250 QC TAB 90° BEND SGL SIDED ⑩	.250 QC TAB 90° BEND DBL SIDED ⑨	.250 QC TAB STRAIGHT DBL SIDED ⑧	.250 QC TAB STRAIGHT SGL SIDED ⑦	.250 QC TAB 45° BEND SGL SIDED ⑥	.187 QC TAB STRAIGHT SGL SIDED ⑤	.250 QC TAB 45° BEND DBL SIDED ④	.187 QC TAB 45° BEND SGL SIDED ③	.187 QC TAB 90° BEND SGL SIDED ②	SSB7 BUSHING ①	NO. OF. POS.	CATALOG NUMBER	PART NUMBER
QUANTITIES																	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± 3°
FINISH
-

DWN
S SCHLGEL
3/5/04

CHK
S YODER
3/5/04

APVD
S YODER
3/5/04

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SSB7CGXX0301

SIZE
A2

CAGE CODE
00779

DRAWING NO
8-796602-0

RESTRICTED TO
-





SCALE
NTS

SHEET
2 of 4





REV
R

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		—	SEE SHEET 1	—	—	—





D




C





B






A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGE	3/5/04	 TE Connectivity			
		CHK S YODER	3/5/04				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S YODER	3/5/04	NAME	
		0 PLC ± -		PRODUCT SPEC		SSB7CGXX0301	
		1 PLC ± -		—			
		2 PLC ± .02		APPLICATION SPEC			
		3 PLC ± .010		—			
		4 PLC ± -		—			
ANGLES		± 3'				SIZE	
MATERIAL		FINISH		WEIGHT		CAGE CODE	
-		-		-		DRAWING NO	
				A2		00779	
				CUSTOMER DRAWING		G-8-796602-0	
						RESTRICTED TO	
						-	
						SCALE	
						SHEET	
						3 of 4	
						REV	
						R	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0						
			—	SEE SHEET 1	—	—	—



5-1546963-8



6-1546963-3



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 3/5/04	TE Connectivity					
		CHK S YODER 3/5/04						
		APVD S YODER 3/5/04	NAME					
DIMENSIONS: INCHES		PRODUCT SPEC	SSB7CGXX0301					
		APPLICATION SPEC						
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
-		-	A2	00779	C=8-796602-0	-		
CUSTOMER DRAWING			SCALE	NTS	SHEET	4 of 4	REV	R