


LOC		DIST		REVISIONS				
EH		00		P	LTR	DESCRIPTION	DATE	OWN
				G		40024028MCO	20NOV2015	RL

D



- ONE CABLE PACKAGED IN A POLY BAG.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- CABLE: SHIELDED 26 AWG, 4 TWISTED PAIRS, 7/34 STRANDED CONDUCTORS, 100 OHMS CAT6A.
- DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.


D

C

C

B

B



				8.53	28	8686.8 (342.00)	2-1933888-8
30.48	100	30632.4 (1206.00)	9-1933888-9	7.92	26	8077.2 (318.00)	2-1933888-6
0.15	0.5	203.2 (8.00)	9-1933888-8	7.32	24	7416.8 (292.00)	2-1933888-4
28.96	95	29108.4 (1146.00)	9-1933888-5	6.71	22	6807.2 (268.00)	2-1933888-2
27.43	90	27584.4 (1086.00)	9-1933888-0	6.1	20	6197.6 (244.00)	2-1933888-0
25.91	85	26060.4 (1026.00)	8-1933888-5	5.49	18	5588.0 (220.00)	1-1933888-8
24.38	80	24536.4 (966.00)	8-1933888-0	4.88	16	4978.4 (196.00)	1-1933888-6
22.86	75	23012.4 (906.00)	7-1933888-5	4.57	15	4673.6 (184.00)	1-1933888-5
21.34	70	21488.4 (846.00)	7-1933888-0	4.27	14	4368.8 (172.00)	1-1933888-4
19.81	65	19964.4 (786.00)	6-1933888-5	3.66	12	3759.2 (148.00)	1-1933888-2
18.29	60	18440.4 (726.00)	6-1933888-0	3.05	10	3149.6 (124.00)	1-1933888-0
16.76	55	16916.4 (666.00)	5-1933888-5	2.74	9	2794.0 (110.00)	1933888-9
15.24	50	15392.4 (606.00)	5-1933888-0	2.44	8	2489.2 (98.00)	1933888-8
13.72	45	13868.4 (546.00)	4-1933888-5	2.14	7	2184.4 (86.00)	1933888-7
12.20	40	12344.4 (486.00)	4-1933888-0	1.83	6	1879.6 (74.00)	1933888-6
11.58	38	11734.8 (462.00)	3-1933888-8	1.53	5	1574.8 (62.00)	1933888-5
10.97	36	11125.2 (438.00)	3-1933888-6	1.22	4	1270.0 (50.00)	1933888-4
10.36	34	10515.6 (414.00)	3-1933888-4	0.92	3	965.2 (38.00)	1933888-3
9.75	32	9906.0 (390.00)	3-1933888-2	0.61	2	660.4 (26.00)	1933888-2
9.14	30	9296.4 (366.00)	3-1933888-0	0.30	1	355.6 (14.00)	1933888-1
METERS, REF	FEET, REF	DIM A	PART NO	METERS, REF	FEET, REF	DIM A	PART NO

A

A

WIRING DIAGRAM 568B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE: 20NOV2015	
DIMENSIONS: mm [INCHES]		R.L. 20NOV2015	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK: F. ZHANG	
0 PLC ± -		NAME: W. FAN	
1 PLC ± -		PRODUCT SPEC: -	
2 PLC ± -		APPLICATION SPEC: -	
3 PLC ± -		WEIGHT: -	
4 PLC ± -		SIZE: A2	
MATERIAL: - 3		CAGE CODE: 00779	
FINISH: -		DRAWING NO: C=1933888	
CUSTOMER DRAWING		RESTRICTED TO: -	
SCALE: NTS		SHEET: 1 of 1	
		REV: G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[3-1906053-4](#)