





.XXX = in
XX.X = mm (REF)

DESIGNED FOR USE WITH .085 S.R.	
CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.088
DIELECTRIC	.066
CONTACT	.025

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
03 ₂	REVISED	DPG 7/23/96	DPG 7/30/96



RECOMMENDED MOUNTING
HOLE

HOUSING MOUNTING NUT LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
HOUSING	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		
FRAC. ± 1/64	DEC. ± .005	ANGLES ± 1°
DRAWN BY B.W.C. DATE 1/27/69		
CHECKED BY P.R.B. 1/27/69		
APPD BY P.R.B. 1/27/69		
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE "OST" STRAIGHT BULKHEAD CABLE JACK DIRECT SOLDER VERSION		
USE ASSY PROCEDURE 408-04720 (31-125) NO. A.P. _____		
SIZE B	CODE IDENT NO. 26805	3104-7985-00
SCALE 4:1	REV 03 ₂	
SHEET 1 OF 1		

CUSTOMER DRAWING

AMP PART # 1057679-1
SHEET 1 OF 1 REV A