


LOC	DIST	REVISIONS			
AG	53	P	LTR	DESCRIPTION	DATE
			F1	REVISED PER ECO-11-004835	11MAR11
				DWN	APVD
				RK	HMR

D






SECTION A—A
SCALE 10:1
10 PLACES

- 1 HOUSING MATERIAL: BLACK THERMOPLASTIC, 94V-O.
- 2 CONTACT MATERIAL: BERYLLIUM COPPER.
- 3 CONTACT PLATED WITH 0.00038 [.000015] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVERALL.
- 4 CONNECTOR MATES WITH 0.5mm [.020] SQUARE POSTS ON 2.0mm [.079] CENTERS, MINIMUM POST LENGTH 2.54 [.100].
- 5 PART NO. DENOTES INDIVIDUAL TWO POSITION SHUNT, WHICH IS PACKAGED ON BREAKAWAY COMBS OF TEN SHUNTS.
- 6 CONTACT PLATED WITH 0.00076 [.000030] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVERALL.
- 7 CONTACT PLATED WITH 0.00381 [.000150] MIN. BRIGHT TIN-LEAD OVER 0.00127 [.000050] MIN. NICKEL OVERALL.

C

B



A

	6	382575-3
	3	382575-2
	7	382575-1
OBSOLETE	FINISH	PART NO 5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.WHITT 1-8-93	TE Connectivity			
DIMENSIONS: MM[INCHES]		CHK R.TALLEY 1-8-93				
		APVD D.HUFFMAN 1-8-93	NAME MINI-SHUNT ASSY, 2mm			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-382575	RESTRICTED TO
1 2		SEE TABLE	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1
					REV F1	