



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , N/A .
© COPYRIGHT N/A BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
DF	SO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			U	REV PER ECO-05-002828	08-05	AA	DE

PART NO.	A	B	C	REMARKS
848077-1	24.00 [609.6]	6.00 [152.4]	-	5
848077-2	192.00 [4876.8]	6.00 [152.4]	-	5
848077-3	48.00 [1219.2]	6.00 [152.4]	-	5
848077-4	12.00 [304.8]	6.00 [152.4]	-	5
848077-5	60.00 [1524.0]	6.00 [152.4]	-	5
848077-6	120.00 [3048.0]	6.00 [152.4]	-	5
848077-7	240.00 [6096.0]	6.00 [152.4]	-	5
848077-8	32.00 [812.8]	6.00 [152.4]	-	5
848077-9	10.00 [254.0]	6.00 [152.4]	-	5
1-848077-0	15.00 [381.0]	6.00 [152.4]	-	5
1-848077-1	80.00 [2032.0]	12.00 [304.8]	12.00 [304.8]	5
1-848077-2	510.00 [12954.0]	6.00 [152.4]	6.00 [152.4]	5
1-848077-3	500.00 [12700.0]	6.00 [152.4]	6.00 [152.4]	5
1-848077-4	103.00 [2616.2]	6.00 [152.4]	6.00 [152.4]	5
1-848077-5	154.00 [3911.6]	6.00 [152.4]	6.00 [152.4]	5
1-848077-6	183.00 [4648.2]	6.00 [152.4]	6.00 [152.4]	5
1-848077-7	571.00 [14503.4]	6.00 [152.4]	6.00 [152.4]	5
1-848077-8	98.50 [2501.9]	6.00 [152.4]	6.00 [152.4]	5
1-848077-9	114.00 [2895.6]	6.00 [152.4]	6.00 [152.4]	5
2-848077-0	555.00 [14097.0]	6.00 [152.4]	6.00 [152.4]	5
2-848077-1	158.00 [4013.2]	6.00 [152.4]	6.00 [152.4]	5
2-848077-2	136.00 [3454.4]	6.00 [152.4]	6.00 [152.4]	5
2-848077-3	72.00 [1828.8]	6.00 [152.4]	6.00 [152.4]	5
2-848077-4	111.00 [2819.4]	6.00 [152.4]	6.00 [152.4]	5
2-848077-5	107.00 [2717.8]	6.00 [152.4]	6.00 [152.4]	5
2-848077-6	147.64 [3750.1]	6.00 [152.4]	6.00 [152.4]	5
2-848077-7	84.00 [2133.6]	6.00 [152.4]	6.00 [152.4]	5
2-848077-8	102.00 [2590.8]	6.00 [152.4]	6.00 [152.4]	5
2-848077-9	108.00 [2743.2]	6.00 [152.4]	6.00 [152.4]	5
3-848077-0	120.00 [3048.0]	6.00 [152.4]	6.00 [152.4]	5
3-848077-1	132.00 [3352.8]	6.00 [152.4]	6.00 [152.4]	5
3-848077-2	360.00 [9144.0]	12.00 [304.8]	12.00 [304.8]	5
3-848077-3	600.00 [15240.0]	6.00 [152.4]	6.00 [152.4]	5
3-848077-4	36.00 [914.4]	6.00 [152.4]	6.00 [152.4]	5
3-848077-5	1195.00 [30353.0]	6.00 [152.4]	6.00 [152.4]	5
3-848077-6	720.00 [18288.0]	6.00 [152.4]	6.00 [152.4]	5
5-848077-3	48.00 [1219.2]	6.00 [152.4]	-	7



1. TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES $[609.6] = \pm 1.2$ $[\pm 3.0]$
24 INCHES $[609.6]$ & UP = $\pm 1\%$
2. MARKED WITH BLACK INK PER MIL-STD-130.
NO MARKING ON 848077-9.
3. TO MATE WITH AMP LGH-3
RECEPTACLE WITH 1.81 $[45.9]$ BARREL DEPTH.
4. OPERATING VOLTAGE: 40 KVDC AT 0 TO 70,000 FEET,
-55°C TO 125°C.
5. PIGTAIL IS SOLDER DIPPED.
6. EQUIPPED WITH #10 RING TONGUE TERMINAL ON GROUND LEAD.
7. INSULATION CUT, BUT NOT REMOVED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 12-NOV-93		tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		CHK S.GLATFELTER 16-NOV-93		LEAD ASSY DBL END, LGH-3 SHIELDED & GLASS BRAID COVERED	
		APVD S.GLATFELTER 16-NOV-93			
		PRODUCT SPEC —			
		APPLICATION SPEC —			
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		SIZE A2	CAGE CODE 00779
		WEIGHT —		DRAWING NO C-848077	RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 of 1
				REV 11	