





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	P		REVISED PER ECO-11-004835	11MAR11	RK HMR



RECOMMENDED P.C. BOARD MOUNTING DIMENSIONS

- HOUSING: FLAME RETARDANT, 94V-0 RATED, GLASS FILLED, NYLON OR POLYESTER, COLOR: BLACK
CONTACTS: PHOS BRONZE.
INSERTS & SCREWLOCKS: ZINC.
- REFER TO APPLICATION SPEC FOR RECOMMENDED P.C. BOARD MOUNTING DIMENSIONS FOR AUTOMATIC INSERTION.
- CONTACTS: SEE TABLE
INSERTS & SCREWLOCKS: CLEAR CHROMATE COATING.
- PLATED WITH GOLD FLASH FOR LENGTH OF .055 MIN FROM MATING END, .000100 MIN TIN ON SOLDER END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- PLATED WITH .000030 MIN GOLD FOR LENGTH OF .055 MIN FROM MATING END, .000100 MIN TIN SOLDER END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.

WITH SCREWLOCKS		5747461-6
WITH SCREWLOCKS		5747461-5
WITH INSERTS		5747461-4
WITH INSERTS		5747461-3
WITH .120 DIA HOLE		5747461-2
WITH .120 DIA HOLE		5747461-1
REMARKS	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. PETERS 16SEP05	 TE Connectivity			
		CHK S. BOLASH 16SEP05				
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY 16SEP05	NAME			
		PRODUCT SPEC	RECEPTACLE ASSY, SIZE 3, 25 POSN, RIGHT ANGLE, .590 SERIES, .026 DIA POSTS, AMPLIMITE HD-20			
	MATERIAL	APPLICATION SPEC	108-40025			
		FINISH	114-40015			
WEIGHT		A1 00779 5747461				
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV P

**COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED**