

## 603331-2 Product Details

[Share](#) [Print](#) [Email](#)

**Detailed product features are not currently available online.**

Product features can often be found by referring to the available documents. [Contact us](#) for information about this product.

No Image Available

### AMPSULATION VFP21, 1.5"X100FT

Always EU RoHS/ELV Compliant (Statement of Compliance)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Contact Us About This Product](#)

**603331-2**

TE Internal Number:  
603331-2  
 Active

[Add to My Part List](#)

[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [Ampsulation VFP21 1-1/2 Inch ID, Black \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [Heat Shrink Tubing \(PDF, English\)](#)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

[List all Documents](#)

#### Related Products:

- [Tooling](#)

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support


[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed



If this document is printed it becomes uncontrolled. Check for the latest revision

REVISIONS		
REV	DESCRIPTION	DATE
C	REVISED PER DCR NO. R060217	03/30/2006



1 TUBING VFP21 MARKED AS SHOWN IN WHITE CHARACTERS ON SURFACE INDICATED

- TUBING VFP21 IS UL RECOGNIZED, IS RATED 125°C [257°F], 600 V AND MEETS VW-1 FLAME TEST.
- TUBING VFP21 IS CSA CERTIFIED AND MEETS VW-1 FLAME TEST.
- WEIGHT PER LINEAR FOOT/304.8 mm: 22.2 g/.049 lbs.
- MATERIAL: BLACK POLYOLEFIN

30.5 m [100 ft] MINIMUM	603331-2
1.22 m [4 ft] MINIMUM	603331-1
LENGTH L	PART NO.

### SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm. INCH DIMENSIONS ARE IN BRACKETS.  DECIMALS .XX ± .01 [0004 in] .X ± .1 [004 in]  ANGLES .X ± 0.5 DEG	DRAWN	UNGUYEN	03/30/2006	Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA, USA 94025 
	APPROVED	JKUSTER	03/30/2006	
	CAD NAME		R060217	
THIRD ANGLE PROJECTION				
SIZE		CODE IDENT. NO.	DWG. NO.	
B		06090	603331	
DO NOT SCALE THIS DRAWING				SHEET 1 OF 1