






LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			E5	REVISED PER ECR-15-011170	07AUG2015	GRZ JL



SECTION A-A
SCALE : 10:1



1. PRODUCT PROVIDED IN STRIP FORM ON REELS; BREAKS MAY BE PRESENT.
2. DIMENSIONS IN BRACKETS ARE IN INCHES.
3. CRIMP WIDTH: .140 F (AMPLIVAR TYPE)
CRIMP HEIGHT (±.002)=(TOTAL CMA+14,600)/243,900

CRIMP WIDTH: .180 F (AMPLIVAR TYPE)
CRIMP HEIGHT (±.002)=(TOTAL CMA+15,000)/286,000

GENERAL APPLICATION GUIDELINES MUST BE FOLLOWED AS SPECIFIED IN CATALOG #82221
FOR APPLICATOR INFORMATION CALL: 1-800-722-1111
FOR PRODUCT INFORMATION CALL: 1-800-522-6752

62308-2
PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA	30JAN06	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK G.D.PORTA	-			
		APVD G.D.PORTA	-	NAME SPLICE, AMPLIVAR 3000-7000 CMA		
		PRODUCT SPEC	-			
MATERIAL REF 0.51±0.03 [.020±.001] BRASS		APPLICATION SPEC	114-2003	SIZE A3	CAGE CODE 00779	DRAWING NO C-62308
		FINISH TIN PL.	-	WEIGHT	SCALE 5:1	RESTRICTED TO -
		CUSTOMER DRAWING			SHEET 1 OF 1	REV E5