




1 PLATED WITH 0.000762 [.000030] GOLD, GOLD FLASH ON THE REMAINDER. GOLD FLASH IS FOR MANUFACTURING PURPOSES ONLY AND AT THE SPECIFIED THICKNESS MAY NOT BE VISIBLE TO THE NAKED EYE.			
2 INLAID GOLD ALLOY			
3 APPLICATOR CUT-OFF 3.05 [.120] MAX			
4 DIMENSION IN BRACKETS ARE IN INCHES.			
5 MEASURED WHEN LEGS ARE COMPRESSED TO ELIMINATE GAP			
OBSOLETE			
62380-4 GOLD 2 NICKEL SILVER, 0.15 [.006] THK 62313-5			
62380-3 GOLD 1 NICKEL SILVER, 0.15 [.006] THK 62313-4			
LOOSE PIECE FORM FINISH MATERIAL PART NO			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm TOLERANCES ON: 2 PL DEC ± 0.38 [.015] 3 PL DEC ± 1° ANGLES ± 1°			
MATERIAL SEE TABLE			
FINISH SEE TABLE			
DR 2/26/87 D HOLLINGSWORTH			
CHK 3/5/87 6 YETTER			
APPD 3/9/87 K RANDOLPH			
APPD 3/9/87 T SHUTTER			
PRODUCT SPEC 108-2010			
APPLICATION SPEC 114-2014			
WEIGHT -			
AMP INCORPORATED Harrisburg, Pa. 17105			
NAME CONTACT, BUTTON, KEYBOARD			
SIZE B FSCM NO 00779 DRAWING NO 62313			
SCALE 10:1 SHEET 1 OF 1			