



1. MAXIMUM INSERTION LOSS: 1.0 dB (1310nm)
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



VIEW A-A

LIGHTRAY MPX CONNECTOR FIBER PATH

0.480±0.030 [18.9±1.2]	6374537-3
2.000±0.051 [78.7±2.0]	6374537-2
1.000±0.051 [39.4±2.0]	6374537-1
L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS 02FEB06	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 02FEB06	NAME			
		APVD F.McCORKEL 02FEB06	PIGTAIL, FIBER OPTIC, SINGLEMODE, (8) 900um BUFFERED FIBER CABLE LIGHTRAY MPX, NO PINS			
		PRODUCT SPEC —	SIZE A2			
		APPLICATION SPEC —				
MATERIAL —	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	FINISH —	CAGE CODE 00779	DRAWING NO C-6374537	RESTRICTED TO —	
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV A	