


printed on 4 Nov 2024 13:50 (Eastern Standard Time) from TE354946



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
			B	REVISED PER E.O. P20338	05NOV2009	RDR
			C	REVISED PER E.O. P20483	28MAY2010	RDR
			C1	REVISED PER ECO-14-016535	31OCT2014	DM
			C2	REVISED PER PCN-24-225053	01OCT2024	CB

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF. ONLY
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04JUN2001 TESFU YOHANNES	TE Connectivity			
DIMENSIONS: INCHES[mm]		CHK 31OCT2014 RUSSELL MESSENGER				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0°30'0"	APVD 31OCT2014 DAVID MEYER	NAME RECEPTACLE 8 WAY FLANGED CONNECTOR -CL07 MOD DT SERIES			
		PRODUCT SPEC 108-151009	SIZE A3 CAGE CODE 4AFU8 DRAWING NO C-DT04-08PA-CL07 RESTRICTED TO -			
MATERIAL 3	FINISH	APPLICATION SPEC 114-151009	SCALE 1:1 SHEET 1 OF 1 REV C2			
		WEIGHT 44.95g	Customer Drawing			