







P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI5942	3-12-99	RDR	RDR
	A	REVISED PER E.O. PI7776	3/24/02	RDR	RDR
	B	REVISED PER E.O. P20078	11-20-08	RDR	RDR
	BI	REVISED PER PCN-22-138488	09MAY2022	MR	IG



7. MATERIAL - HOUSING: PA66 GF15 (GRAY); GROMMET/SEAL: VMQ (RED/ORANGE)
6. CONTACT FACTORY FOR SAE J1939-15 CONNECTOR USAGE.
5. THIS RECEPTACLE MATES WITH DTM06-2S-**** PLUG.
(**** = ALL MODIFICATIONS)
4. INTERNAL RESISTOR: 110Ω MIN., 120Ω NOM., 130Ω MAX., .4 WATTS MIN..
3. SECONDARY WEDGE LOCK IS INCLUDED WITH RECEPTACLE.
2. DELETED.
1. DELETED.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTAL 05FEB2001	 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK V. TOMSA 13FEB2001			
		APVD R. REED 15FEB2001			
		PRODUCT SPEC 108-151010			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-151010	NAME RECEPTACLE, A KEY 2 CONTACTS W/ RESISTOR COLOR: GREY DTM SERIES		
MATERIAL 7		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO G-DTM04-2P-P006
FINISH -		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	RESTRICTED TO -
				REV BI	