







	NC	NEW RELEASE PER E.O. AI4874	21JUL1995	-	RDR
	A	REDRAWN AND REVISED PER E.O. PI7133	15FEB2001	-	RDR
	AI	REVISED PER PCN-22-136768	21APR2022	MR	IG



3D VIEW



RECEPTACLE HOUSING

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIDE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.2]

6. MATERIAL: HOUSING: PA66 GF15 (GRAY)
GROMMET: VMQ (RED/ORANGE)
5. THIS RECEPTACLE MATES WITH DTM06-2S-XXXX PLUG.
(XXXX = ALL MODIFICATIONS)
4. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
3. ITEM SOLD SEPARATELY: WM-2P.
2. DELETED.
1. DELETED.

NOTE: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES [mm]

MATERIAL

6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±.025 [0.64]

4 PLC ±

ANGLES ±

FINISH -

DWN J.APOSTOL 05FEB2001

CHK V.TOMSA 13FEB2001

APVD R.REED 15FEB2001

PRODUCT SPEC 108-151010

APPLICATION SPEC 114-151010

WEIGHT 5 G

Customer Drawing

TE Connectivity

NAME RECEPTACLE 2 PIN CONT. #20
DTM SERIES -

SIZE A3

CAGE CODE -

DRAWING NO. ©-DTM04-2P

RESTRICTED TO -

SCALE 2:1

SHEET 1 OF 1

REV AI