

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. P17591	17SEP2002	-	RDR
	C	REVISED PER E.O. P18449	04FEB2004	-	RDR
	C1	REVISED PER PCN E-20-013840	18SEP2020	MK	IG
	C2	REVISED PER ECR-22-127978	02FEB2022	HD	IG

Ø 1.750±.025
[44.45±.63]

MAIN POLARIZING KEYWAY

1.625
[41.28]

Ø 1.329
[33.76]

1.648
[41.86]

1.030
[26.16]

.505
[12.83]

.100
[2.54]

1.220
[30.99]

6

HDP24-18XXPSX
201816

1.500 - 18 UNEF
REF. THREAD

Ø 1.507±.005
[38.28±.12]

1.442^{+.010}_{-.000}
[36.63^{+.25}_{-.00}]

RECOMMENDED MOUNTING HOLE

6 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS. (14=2014)
MONTH: THIRD DIGIT, EXCLUDING 1.A=JAN., B=FEB., C=MARCH...(K=OCT.)
DAY: FOURTH AND FIFTH DIGIT (14=14th DAY)
HOUR: SIXTH AND SEVENTH DIGIT (11=11AM)


5. THIS PART MATES WITH HDP26-18-**S/P*-***** (***** = ALL MODIFICATIONS,
* = TYPE OF SEAL.)

4. FOR ARRANGEMENT OF CONTACT LOCATION
SEE ENVELOPE DRAWING 0425-013-1800.

3. FOR CONTACTS, WIRES, CONNECTOR PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000 AND
0425-021-0000.

2. RECOMMENDED PANEL THICKNESS: .062[1.58] TO .187[4.76].

1. THIS RECEPTACLE TO BE USED WITH 2411-002-1805 (PLASTIC) C2
PANEL NUT AND 2414-002-1886 LOCK WASHER.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.BEARD	12JAN2000	 TE Connectivity		
		CHK J.LIM	04FEB2004			
DIMENSIONS: INCH [MM]		APVD S.BEARD	16JAN2004	NAME RECEPTACLE CONNECTOR SHELL SIZE 18 BAYONET COUPLING HDP20 SERIES		
		PRODUCT SPEC	108-151015			
		APPLICATION SPEC	114-151015			
MATERIAL		WEIGHT	20.4 g	SIZE A3	CAGE CODE 00779	DRAWING NO C-HDP24-18-XXPSX
		CUSTOMER DRAWING		SCALE 2.000	SHEET 1 OF 1	REV C2