


RP73D2A6K04BTG Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



RP73D2A6K04BTG
(1-1879276-0)

TE Internal Number: 1-1879276-0

[Active](#)

Fixed Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Fixed Resistor
- Resistor Type = Precision Resistor
- Resistance Selection = K Ω
- Resistance = 6.04K Ω
- Power Rating = .125 W

[View all Features](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [SMD Precision Resistors - Type RP73 Series - Tyco El...](#) (PDF, English)
- [8-1773459-4 POWER FILTERING AND RESISTIVE SOLUTIONS ...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Fixed Resistor
- Resistor Type = Precision Resistor
- [Element](#) = Thin Film
- [Series](#) = RP73
- Termination Type = Solder

Electrical Characteristics:

- [Resistance Selection \(\$\Omega\$ \)](#) = K
- [Resistance \(\$\Omega\$ \)](#) = 6.04K
- [Power Rating \(W\)](#) = 0.125
- [Tolerance \(%\)](#) = 0.1
- [Package Type](#) = Cut Tape Length

Body Features:

- [Mount Style](#) = Surface Mount
- [Packaging Style](#) = 0805
- [Package, Component Size](#) = 2.1 x 1.3

Configuration Features:

- [Number of Terminations](#) = 2
- [Number of Resistors](#) = 1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = ± 15

Operation/Application:

- [Application](#) = Precision

Other:

- Brand = Holsworthy

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

