

Specification Status: RELEASED

Electrical Rating

Voltage: 16V_{DC} MAX

Current: 40A MAX

Insulating Material:

Cured Flame Retardant Epoxy Polymer meets
UL 94-V-O Requirements

Lead Material:

24 AWG Tin Lead Plated Nickel Copper Alloy

Marking:

 Manufacturer's Mark and Voltage
 R 090 — Part Identification
 Lot Identification (can be on back)




TABLE I. DIMENSIONS:

	A		B		C		D		E	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	--	7.4	--	12.2	4.3	5.8	7.6	--	--	3.1
in*:	--	(0.29)	--	(0.48)	(0.17)	(0.23)	(0.30)	--	--	(0.12)

TABLE II. PERFORMANCE RATINGS :

I HOLD RATED CURRENT	CURRENT RATINGS		INITIAL RESISTANCE VALUES		ONE HOUR POST-TRIP RESISTANCE STANDARD TRIP	TIME TO TRIP @ 8A	TRIPPED- STATE POWER DISSIPATION
AMPERES AT 20°C HOLD	AMPERES AT 20°C		OHMS AT 20°C		OHMS AT 20°C MAX	SECONDS AT 20°C	WATTS AT 20°C
	HOLD	TRIP	MIN	TYP			
0.90	0.90	1.80	0.07	0.10	0.18	1.2	0.6

Recognitions:

Reference Documents:

Precedence:

Effectivity:

CAUTION:

UL, CSA, TUV recognized.

PS300

This specification takes precedence over documents referenced herein.

Reference documents shall be the issue in effect on the date of invitation for bid.

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.