

TY-type Twin Wheel Caster






Characteristic

Small and light weight caster with excellent driving stability and turning ability.
Having original appearance, it suits for any kind of interior device. New stopper is applied to obtain better operability.



Application

Medical instruments /
Office automation appliances /
Audio racks / TV tables /
Various types of wagons, etc.

TY40N□S / TY50N□S (with stopper)



TY40S / TY50S (with stopper)



Specification

Model No.	Material		Allowable Load (kg)	Code No.
	Body	Wheel		
TY40	PA	PA	40	19011
TY40S				19021
TY40N2.5				19012
TY40N2.5S				19022
TY40N3				19013
TY40N3S				19023
TY40N8				19014
TY40N8S				19024
TY40N10				19015
TY40N10S				19025
TY50	PA	PA	60	19016
TY50S				19026
TY50N3				19017
TY50N3S				19027
TY50N8				19018
TY50N8S				19028
TY50N10				19019
TY50N10S				19029
TY50N12				19020
TY50N12S				19030

Size List

Model No.	A	B	C	D	E	G	d	H1	H2	J1	J2	K	L	W1	W2		
TY40	42	φ28	φ39	φ40	15	φ5		49		t2.6				44	20		
TY40S																	
TY40N2.5							W5/16—18										
TY40N2.5S																W3/8—16	
TY40N3																	M8×1.25
TY40N3S																	
TY40N8							12										
TY40N8S																14	
TY40N10																	19
TY40N10S																	
TY50	49	φ40	φ54	φ50	17	φ5.5		65	t3			49	21				
TY50S																	
TY50N3							W3/8—16										
TY50N3S														M8×1.25			
TY50N8															M10×1.5		
TY50N8S																19	
TY50N10							14										
TY50N10S														17			
TY50N12															14		
TY50N12S																	

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.