


TOLERANCE UNLESS SPECIFIED =

.XXX= +/- .005

.XX= +/- .015


FRACTIONS= +/- .032

28-180.DC2





1.06
MTG

XXXX
VDE REG. NO.




115/230V
50/60 HZ

5VA



PC PINS .025 SQ



PRODUCTION TESTS

URNS RATIO =100%

DC RESISTANCE IN OHMS	1-3 =	340 NOM
	4-6 =	408 NOM
	7-9 =	10.3 NOM
	10-12 =	12.1 NOM

MAX EXCITATION CURRENT = .016 A

APPLY 230V 60HZ 1-6 (3+4)

PRI WDGS 114.5 TO 115.5 V

SEC WDGS 17.7 TO 18.5 V

HIPOT: 4000V P-S

4000V P,S, TO CORE

600V P-P, S-S