



# TRIPLETT

*Test Equipment & Tools*



## POCKET REFERENCE

**TPAL-001****Professional AutoLoader**

Autoloading Screwdriver w/6 selectable bits contained in a heavy duty steel shaft

- 3 Philips and 3 standard bits are pre-Loaded
- Magnetized shaft
- Bits are interchangeable with any standard 1/4" drive bit

**TMAL-001****Mini AutoLoader**

Autoloading Screwdriver with 6 self contained Precision bits

- 3 Philips and 3 standard bits are pre-Loaded
- Magnetized shaft
- Bits are replaceable

**TBK-001****Industrial Bit Kit**

32 piece Industrial Grade, 1/4" bit kit made of S2 steel

- All bits fit the Professional AutoLoader for replacement or substitution
- Kit includes: 30 S2 Steel Bits, quick release drill adapter, hex to socket adapter, carrying case w/ belt clip

**TSBK-001****Security Bit Kit**

32 piece Industrial Grade, 1/4" bit kit for tamper proof fasteners

- All bits fit the Professional AutoLoader for replacement or substitution
- Kit includes: 30 S2 Steel Bits, quick release drill adapter, hex to socket adapter, carrying case w/ belt clip



**TT-220****7" KlikGrip**

7" auto adjusting pliers

- Adjusts with only one hand
- Lightweight, strong and versatile
- Non-slip handles

**TT-221****10" KlikGrip**

10" auto adjusting pliers

- Adjusts with only one hand
- Lightweight, strong and versatile
- Non-slip handles

**TT-230****PowrJaw Electrician's Pliers**

8" Electrician's Pliers with Ergonomic Cushion Grips


- PowrJaw delivers 100% gain in gripping power
- High Strength CRV Jaws
- Pearl nickel finish resists corrosion
- Spring loaded and lockable handles

**TT-231****PowrJaw Diagonal Pliers**

7.5" Diagonal Cutting Pliers with Ergonomic Cushion grips

- PowrJaw delivers 100% gain in cutting power
- High Strength CRV Jaws
- Pearl nickel finish resists corrosion
- Spring loaded and lockable handles




**TT-200**
**LongLockers**

Extended reach 15" Locking pliers with cushioned grips

- Universal jaw design fits any application
- Narrow jaws fit into tight spaces
- Standard grip size makes operation easy

**9610**
**Plug-Bug 2**

GFCI Receptacle Tester

- Detects common wiring problems
- Push button GFCI test
- Easy to follow graphic explains how to read fault codes


**PT12**
**ProTemp 12**

Non-Contact 12:1 Infrared Thermometer

- Single handed, fast and accurate temperature readings
- Laser pinpoints measurement area
- Backlit display makes reading measurements easy

**TLT-160**
**LaserTape 160**

Non-Contact Laser Measurement  
from 2"-160' accurate to 0.060"

- Easily calculate square footage, volume, and simple trig functions
- Add or subtract measurements
- 20 memory locations to save measurements




**TT-110**
**GrabLite**

6 High Intensity LED's  
and 21" Telescoping Flex End Magnet

- Rare earth magnet allows for greater lifting capacity
- Runs on only 1-AA battery
- Wrist strap and carrying case included

**TT-120**
**ClipLite**

Cap Light with High Intensity White and Red LEDs  
and adjustable position

- Over visor design won't impair vision
- Adjustable angle puts light where it's needed
- Flashing LEDs improve safety for joggers


**TT-130**
**BugLite**

Magnetic Base Multi-purpose light



- 2 high powered LEDs
- Hi strength Neodymium Magnetic base attaches to flats, curves, or corners
- Attaches directly to tools
- Lightweight tough aluminum body

**TT-101**
**FUEZR**

Multi-purpose LED Work Lite w/case

- 27 Bright white LEDs
- Selectable 24 LED Flood light or 3 LED Flashlight
- SilkGrip Non Slip Finish
- Self storing Hanger and adjustable stand
- 3 axis Magnet arrangement to attach to metal




**8000**
**CamView PTZ**

Multi-Function Test Tool for CCTV &amp; Security Installers

- Full color 2.6" TFT-LCD Video Monitor
- Supports RS-485, RS-422 & RS-232 PTZ interfaces
- Supports more than 25 PTZ Protocols
- 10 hour rechargeable battery

**8050**
**CamView W35**

 Security Wrist Monitor  
 with 3.5" Display

- View camera output to adjust zoom, focus, position, etc.
- Verify quality of video signal
- High Brightness, daylight viewable display
- 6 hour rechargeable battery


**8105**
**CobraCam USB 2**

Portable Inspection Camera with USB Interface

- Waterproof snake – bend to fit any application
- New ZOOM function
- Snapshot and Live Video capable
- Works with Windows OS

*\*Not MAC compatible*

**8115**
**CobraCam 2**

 Portable, Self Contained, Inspection Camera  
 and Video Monitor

- 6' Flexible snake allows access to hidden locations
- 2 high intensity LED's for lighting
- Extend up to 100 feet of watertight length



**CC2-CAM3FM****3' x 5.5mm Camera**

3' snake with 5.5mm camera head for CobraCam2



- 5.5mm head fits into small areas
- Super flexible 3 foot snake is easier to control
- Self-contained LED lighting
- Water proof connections

**CC2-CAM3F****3' x 10.2mm Camera**

3' snake with 10.2mm camera head for CobraCam2

- 3 foot, semi-rigid snake is easier to control
- Self-contained LED lighting
- Water proof connections

**CC2-CAM6F****6' x 10.2mm Camera**

6' snake with 10.2mm camera head for CobraCam2



- Standard 6 foot, semi-rigid snake for added reach
- Self-contained LED lighting
- Water proof connections

**CC2-CAM10F****10' x 10.2mm Camera**

10' snake with 10.2mm camera head for CobraCam2

- 10 foot, semi-rigid snake for extended reach
- Self-contained LED lighting
- Water proof connections



**CC2-XC3F**
**3' Extension Cable**

Extend the usefulness of your CobraCam2



- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections

**CC2-XC6F**
**6' Extension Cable**

Extend the usefulness of your CobraCam2

- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections


**CC2-XC10F**
**10' Extension Cable**

Extend the usefulness of your CobraCam2

- Cable extension adds a longer reach to your existing CobraCam2 camera
- Combine cables to extend up to 100'
- Water proof connections


**1101**
**1101-B Digital MultiMeter**

Compact DMM with Backlit display and Temperature test

- 3 1/2 digit backlit display
- 20 Ranges & Functions: AC/DC Voltage, DC Current to 10A, Resistance, and Continuity
- Shock absorbing case with stand






**2030**
**2030-C Pocket Sized DMM**
**Auto-ranging Pocket Sized DMM**

- 37 Ranges and Functions: AC/DC Voltage to 600V, Current, Resistance, Capacitance and Frequency ranges
- Convenient compartment holds test leads securely
- Closing the cover ensures the unit is off, Preserving battery life

**9007**
**9007 Digital MultiMeter**
**Huge 1.4" Backlit display DMM  
w/capacitance**

- 3 1/2 digit backlit display
- 31 ranges including: Voltage, Current to 20A, Resistance, and Continuity
- Shock absorbing, overmolded case w/ stand


**9045**
**9045**
**True RMS DMM with  
Temperature, Capacitance, and Frequency**

- 6000 count auto ranging True RMS DMM
- AC/DC Voltage & Current, Resistance ranges
- Backlit display with 61 segment bargraph
- Shock absorbing, overmolded case w/stand


**9055**
**6-in-1 EnviroMeter**
**Autorangeing DMM with multiple Environmental functions**

- Built-in Light (Lux) and Sound Level (dB)
- Built-in Temperature and Relative Humidity
- Non-contact AC Voltage Detector
- 4000 count, fully annunciated, backlit display
- Shock absorbing, overmolded case w/ stand




**TSC-MC1**
**SoniChek MC**

Mini Sound Level Meter

- C weighted reads 40-130dB from 31.5Hz-8KHz
- Measure sound level for PA, Home Theater, Alarm, Sound Systems, etc.
- Also features Min/Max and backlit display

**3279**
**CableRater**

dB Loss Measurement System

- Measure dB loss through passive and active components
- Verify installation before cable TV service is connected
- Test cables, splitters, amplifiers, etc.


**3375**
**Fox Jr. & Hound Jr.**

Compact Wire and Cable Tracing Kit

- The compact design allows you to Identify, Locate and Trace wires inside tight locations
- Adjustable warble tone
- RJ-11/RJ-45 and Alligator Clip connections


**3388**
**HotWire Fox & Hound**

Live Wire Circuit Tracing Kit

- Identify, Locate, and Trace Energized wires from 1V to 220V
- Trace wires up to 1000 feet in length
- Locates wires up to 3 feet away in open air
- Includes modular leads & hard-sided carrying case




**3399**
**Fox 2 & Hound 3 Kit**
**Deluxe Wire & Cable Tracing Kit**

- Identify, Locate, and Trace wires inside wall bays and wire runs with TrueTrace technology
- Use in houses, factories, boating, and more

**9601**
**Sniff-It 2**
**Non-Contact AC Voltage Detector with Adjustable Sensitivity**

- Detects from 5-600 Volts AC
- Pocket sized for convenience
- Light and Tone vary with proximity to voltage


**3274**
**WireMaster Coax**
**8-Way Coaxial Cable Mapper**

- ID up to 8 cables with included BNC remotes
- Test for Opens, Shorts, & Overvoltage
- A must for CCTV, Security, and Surveillance System Installers


**3281**
**WireMaster Mapper**
**8-Way Wire & Cable Mapping Kit**

- Quickly map all types of cables using the included 39 remotes and adapters
- Includes 8 each: BNC, F, RJ-11/RJ-45, and Alligator Clip Remotes plus Carrying Case




**9615**
**Line-Bug 4**

Phone / LAN Jack tester

- Test for phone line connection and polarity
- RJ-11 or RJ-45 interface
- Protect your expensive LAN tester from damaging telephone current

**9650**
**Breaker Sniff-It**

Digital Circuit Breaker Identifier

- Positively identifies circuit breakers without making adjustments
- Micro-processor controlled reduces false readings
- 90-280 VAC operation


**3240**
**PairMaster**

LAN Cable Test Set w/2 Remotes

- Test and map Cat 5 or Cat 6 cables with the press of a button
- Test for 8 Faults: Open, Short, Crossed, Split, Reversed, Transposed, Overvoltage, Double Split (NEXT)


**3241**
**PairMaster Kit**

 LAN Cable Cable Testing Kit  
 w/16 Remotes and Carrying Case

- Test and map Cat 5 or Cat 6 cables with the press of a button
- Test for 8 Faults: Open, Short, Crossed, Split, Reversed, Transposed, Overvoltage, Double Split (NEXT)





**3256**

**WireMaster HDMI-2**

High Definition Cable Tester

- Tests HDMI cables including v1.4
- Automatic and Manual test modes
- Lightweight and easy to use
- Carrying case included

**3254**

**WireMaster XR-2**

LAN Cable Test Set with Tone Generator

- Test installed LAN cables or patch cables
- RJ-11 & RJ-45 connections
- Generates tracer tone



**3260**

**WireMaster XR-5**

5 Cable Test Set

- Test 5 wire types: RJ-11, RJ-45, BNC, Firewire, and USB
- Test installed wiring or patch cables
- Simple one button test confirms good cable or identifies faults



**3271**

**TDR Cable Fault Finder**

Digital Cable Length Meter  
& Tone Generator

- Easily find distance to fault or cable length from one end
- Test all types of communication cables
- 39 standard cable presets or manual selection




**9200**
**Model 9200-A**
**Mini AC Clamp-on meter**

- Measure AC Amps from 0-300 amps
- Sensitive 20A range w/ 0.01 amp resolution
- Data Hold Function
- Carrying case included

**9310**
**Model 9310-A**
**AC/DC Clamp-on Meter  
w/Temp, Cap, Freq and Backlit display**

- Measure AC/DC Current to 1000A
- Auto Ranging DMM measurements include: AC/DC Voltage, Capacitance, Resistance, Diode, Frequency and Temperature
- Data Hold and Relative functions


**9320**
**Model 9320-A**
**True RMS AC/DC Clamp-on Meter  
w/Temp, Cap, Freq and Backlit display**

- Measure AC/DC Current to 1000A
- Auto Ranging DMM measurements include: AC/DC Voltage, Capacitance, Resistance, Diode, Frequency and Temperature
- Data Hold and Relative functions


**79-812**
**ModuLead**
**Premium Modular Test Leads**

- Universal Design Fits Most Digital Multimeters
- UL Listed Premium Silicone Jacketed Wire with Banana Plugs
- Includes: 2 Pointed Probes, 2 Flat Probes, 2 Alligator Clips, 2 24" Leads, 2 60" Leads, Tri-Fold Carrying Case
- Lifetime Limited Warranty




**3018**
**Model 310**
**Analog Hand Sized VOM**

- VOM w/18 Ranges and Functions

**Also Available:**

- 3022 – 310C: Analog VOM w/18 Ranges and polarity reversing switch for DC ranges
- 3067 – 310-Tel: Analog VOM w/16 Ranges and polarity reversing switch for DC ranges

**3145**
**Model 60**
**Ruggedized VOM – 28 Ranges**

- 3 fuse design for a high level of protection
- 6" Mirrored scale reduces parallax error
- Confidence test to check batteries, fuses, leads, and meter accuracy
- High Impact Ruggedized case


**3030**
**Model 630**
**Classic VOM – 25 Ranges**

- Fuse and Diode overload protection
- 6" Mirrored scale reduces parallax error
- Decibel Scale for Audio
- AC/DC Volts, Resistance and DCmA

**2010**
**Model 2000**
**Railroad Test Set**

Measures AC/DC Voltage & Current, Resistance, Code Parameters, and Relay Contact On Time

**Also Available:**

- 2011 – 2001: w/100HZ and 250HZ cab filters
- 2012 – 2002: w/100HZ and 200HZ cab filters
- 2013 – 2003: w/60HZ and 250HZ cab filters





# **TRIPLETT**

***Test Equipment & Tools***

***100+ Years of Quality and Commitment***



**WWW.TRIPLETT.COM**  
**1-800-TRIPLETT**

Triplett Test Equipment & Tools

850 Perimeter Rd

Manchester, NH 03103

