




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX STYLE:	2499-003
Capacitance Value:	1500 pF
Capacitance Tolerance:	+20%
Temp. Characteristics:	X5S
Rating:	500 WVDC @ 85°C
Current (A):	20
IR Min @ 100 vdc	10 GΩ
DWV	1500 VDC
Operating Range:	-55° TO + 85°C

NOTES:

- SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.
- TUSONIX STANDARD PART
 NUMBER: 2499-003-X5S0-152M.
 TUSONIX R.o.H.S. COMPLIANT PART
 NUMBER: 2499-003-X5S0-152M LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: TRADEMARK, CAPACITANCE CODE AND TOLERANCE CODE STAMPED ON BUSHING HEX FLATS:
 STANDARD PART: BLACK MARKING.
 RoHS COMPLIANT PART: GREEN MARKING.

X-2015 Rev-0

REVISION RECORD Original Release C.O. 19980605-5-01 DIM'S IN METRIC & NOTE ADDED, SPEC. TABLE REVISED L.E. 01-27-04 20040126-2-07 ADDED NOTES 2 & 3. DIM 051 METRIC WAS 1.29. S.M. 07-24-06 20060712-1-06 REDRAWN BUSHING WITH SHOULDER. S.M. 08-09-06 20060728-2-09	0	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .015 [0.38] ANGLES ±	Title BUSHING TYPE FEED-THRU CAPACITOR	
	1		Drawn S.M. 06-05-98	Scale 3 X
	2		Approved J.Mc. 06-05-98	
	3		A 2499-003-X5S0-152M	
		TUSONIX TUCSON, ARIZONA		