

- Replacement for low voltage 20 W halogen lamp
- Dimmable
- Lifetime of 35,000 hrs
- Built-in TCS (Temperature Control System)
- Ideal for accent lighting at home, in hotels or restaurants



Order Code 52026

General Data

Lamp Socket GU5.3

Design Lens

Geometric Data

Length (mm) 50

Diameter (mm) 48.5

Weight (g) 50

Electric Data

Wattage 6.5 W

Voltage 12 V AC/DC

Power Factor ≥ 0.65

Operating Frequency 50/60 Hz

Photometric Data

Luminous Flux (lm) 275

CRI ≥ 75

CCT 4200 K – neutral white

Luminous Intensity (cd) 1100

Beam Angle (°) 30°

Lifetime 35 000hrs

Equivalent to (W) 20 W





Order Code 52026

Product Description LED MR16 GU5.3 6W 12V AC/DC 4200K NW 275LM DIM Box

Technical Packaging Details

Barcode	023942520269
EAN 128	(02)00023942520269(37)40(91)162
EAN 14	50023942520264
Pack Dimensions	62 mm x 50 mm x 50 mm
Pack Weight	65 g
Carton Qty (Shipping Unit)	10
Carton Dimensions (HxWxL)	330 mm x 300 mm x 150 mm
Cartons/Layer	51
Layers/Pallet	6
Units/Pallet	2040

Photometric Diagram

52026

