


Premium Enhanced Cat.5e Patch Cables

Premium Enhanced Cat.5E Patch Cables

Available in 14 colours the extensive range of patch cables are designed for new generation networking. Each cable is manufactured to the highest standards and specification from stranded Cat.5E cable and 50 micron gold plugs. They are fully tested and fitted with short bodied connectors and integral strain relief boots.

Features:

- Designed for advanced bandwidth frequency systems & increased network speeds
- Manufactured using quality component parts:
Connectors: 50 micron gold RJ45 plugs, Cable: UL approved Cat.5 Enhanced stranded cable
- To reduce crosstalk, short bodied connectors maintain speed & data integrity
- Moulded design suitable for advanced and new build



Length	Beige	Blue	Red	Green	Yellow	Black	White
0.3m	2965-0.3	2965-0.3B	2965-0.3R	2965-0.3G	2965-0.3Y	2965-0.3BK	2965-0.3W
0.5m	2965-0.5	2965-0.5B	2965-0.5R	2965-0.5G	2965-0.5Y	2965-0.5BK	2965-0.5W
0.75m	2965-0.75	2965-0.75B	2965-0.75R	2965-0.75G	2965-0.75Y	2965-0.75BK	2965-0.75W
1m	2965-1	2965-1B	2965-1R	2965-1G	2965-1Y	2965-1BK	2965-1W
1.25m	2965-1.25	2965-1.25B	2965-1.25R	2965-1.25G	2965-1.25Y	2965-1.25BK	2965-1.25W
1.5m	2965-1.5	2965-1.5B	2965-1.5R	2965-1.5G	2965-1.5Y	2965-1.5BK	2965-1.5W
2m	2965-2	2965-2B	2965-2R	2965-2G	2965-2Y	2965-2BK	2965-2W
3m	2965-3	2965-3B	2965-3R	2965-3G	2965-3Y	2965-3BK	2965-3W
5m	2965-5	2965-5B	2965-5R	2965-5G	2965-5Y	2965-5BK	2965-5W
8m	2965-8	2965-8B	2965-8R	2965-8G	2965-8Y	2965-8BK	2965-8W
10m	2965-10	2965-10B	2965-10R	2965-10G	2965-10Y	2965-10BK	2965-10W
15m	2965-15	2965-15B	2965-15R	2965-15G	2965-15Y	2965-15BK	2965-15W
20m	2965-20	2965-20B	2965-20R	2965-20G	2965-20Y	2965-20BK	2965-20W
30m	2965-30	2965-30B	2965-30R	2965-30G	2965-30Y	2965-30BK	2965-30W

Length	Orange	Purple	Gold	Silver	Imac Blue	Pink	Brown
0.3m	2965-0.3RG	2965-0.3PR	2965-0.3AU	2965-0.3AG	2965-0.3IM	2965-0.3PK	2965-0.3BR
0.5m	2965-0.5RG	2965-0.5PR	2965-0.5AU	2965-0.5AG	2965-0.5IM	2965-0.5PK	2965-0.5BR
0.75m	2965-0.75RG	2965-0.75PR	2965-0.75AU	2965-0.75AG	2965-0.75IM	2965-0.75PK	2965-0.75BR
1m	2965-1RG	2965-1PR	2965-1AU	2965-1AG	2965-1IM	2965-1PK	2965-1BR
1.25m	2965-1.25RG	2965-1.25PR	2965-1.25AU	2965-1.25AG	2965-1.25IM	2965-1.25PK	2965-1.25BR
1.5m	2965-1.5RG	2965-1.5PR	2965-1.5AU	2965-1.5AG	2965-1.5IM	2965-1.5PK	2965-1.5BR
2m	2965-2RG	2965-2PR	2965-2AU	2965-2AG	2965-2IM	2965-2PK	2965-2BR
3m	2965-3RG	2965-3PR	2965-3AU	2965-3AG	2965-3IM	2965-3PK	2965-3BR
5m	2965-5RG	2965-5PR	2965-5AU	2965-5AG	2965-5IM	2965-5PK	2965-5BR
8m	2965-8RG	2965-8PR	2965-8AU	2965-8AG	2965-8IM	2965-8PK	2965-8BR
10m	2965-10RG	2965-10PR	2965-10AU	2965-10AG	2965-10IM	2965-10PK	2965-10BR
15m	2965-15RG	2965-15PR	2965-15AU	2965-15AG	2965-15IM	2965-15PK	2965-15BR
20m	2965-20RG	2965-20PR	2965-20AU	2965-20AG	2965-20IM	2965-20PK	2965-20BR
30m	2965-30RG	2965-30PR	2965-30AU	2965-30AG	2965-30IM	2965-30PK	2965-30BR