


CECC (E) 40401-010 Qualified Thin Film Chip Resistors




DESIGN SUPPORT TOOLS

[click logo to get started](#)


Utilizing proven expertise in Thin Film resistors, VISHAY provides a CECC qualified chip with the same reliability and stability found in QPL resistors. These chips are available in a wide range of sizes, values and performance characteristics.

CONSTRUCTION



FEATURES

- Nickel barrier for high temperature operating conditions
- Tight TCR < 10 ppm/°C, and in lot tracking < 5 ppm/°C in (-55 °C, +155 °C temperature range)
- Very low noise < 35 dB and voltage coefficient 0.1 ppm/V
- Non-inductive
- Laser trimmed down to 0.1 %
- Wraparound resistance less than 0.01 Ω
- Antistatic waffle-pack or tape and reel packaging available
- High stability (0.05 % - 1000 h at Pn at +70 °C)
- Withstand moisture resistance test of AEC-Q200
- Conform to EN 140401 804
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE	RESISTANCE RANGE ^{(1) (2)} Ω	RATED POWER Pn W	LIMITING ELEMENT VOLTAGE (UL) V	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
RV E	0505	100 to 260K	0.125	50	0.1, 0.5, 1, 2, 5	10, 25
RV E	0603	100 to 260K	0.125	50	0.1, 0.5, 1, 2, 5	10, 25
RV E	0805	100 to 300K	0.200	50	0.1, 0.5, 1, 2, 5	10, 25
RV E	1206	100 to 1M	0.330	75	0.1, 0.5, 1, 2, 5	10, 25

Notes

(1) Extended resistance range on request

(2) For ohmic range versus tolerance and TCR, see detailed table

CLIMATIC SPECIFICATIONS

Operating temperature range	-55 °C to +155 °C
Storage temperature range	-55 °C to +155 °C

MECHANICAL SPECIFICATIONS

Resistive material	Nichrome
Substrate material	Alumina
Plating	Tin lead over nickel or tin silver over nickel or gold over nickel
Marking resistance to solvents	Per CECC Specs

OHMIC RANGE VS. TOLERANCE AND TCR


CASE SIZE	OHMIC RANGE Ω	TOLERANCE %	TCR ppm/°C
0505	100 < 500	0.5; 1; 2; 5	10, 25
0505	500 to 260K	0.1; 0.5; 1; 2; 5	10, 25
0603	100 < 500	0.5; 1; 2; 5	10, 25
0603	500 to 260K	0.1; 0.5; 1; 2; 5	10, 25
0805	100 < 500	0.5; 1; 2; 5	10, 25
0805	500 to 300K	0.1; 0.5; 1; 2; 5	10, 25
1206	100 < 500	0.5; 1; 2; 5	10, 25
1206	500 to 1M	0.1; 0.5; 1; 2; 5	10, 25

TECHNICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Absolute TCR	E: ± 25 ppm/°C / Y: ± 10 ppm/°C	-55 °C to +155 °C
Absolute tolerance	± 0.1 %, ± 0.5 %, ± 1 %, ± 2 %, ± 5 % (R ≥ 500 Ω) ± 0.5 %, ± 1 %, ± 2 %, ± 5 % (R ≥ 100 Ω)	
Voltage coefficient	0.1 ppm/V	
Noise	-35 dB typical	
Thermal EMF	< 0.1 µV/°C	
Load life stability	± (0.1 % Rn ⁽³⁾ ± 0.05 Ω)	1000 h Pn at +70 °C

Note

(3) Rn: Nominal resistance

DIMENSIONS in millimeters (inches)


SERIES/ CASE SIZES	A		B		D/E		C	
	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.
RV 0505	1.198 (0.047)	1.502 (0.059)	1.143 (0.045)	1.397 (0.055)	0.250 (0.010)	0.510 (0.020)	0.373 (0.015)	0.627 (0.025)
RV 0603	1.368 (0.054)	1.672 (0.066)	0.623 (0.025)	0.877 (0.035)	0.250 (0.010)	0.510 (0.020)	0.373 (0.015)	0.627 (0.025)
RV 0805	1.758 (0.069)	2.062 (0.081)	1.143 (0.045)	1.397 (0.055)	0.250 (0.010)	0.510 (0.020)	0.373 (0.015)	0.627 (0.025)
RV 1206	2.908 (0.114)	3.212 (0.126)	1.473 (0.058)	1.727 (0.068)	0.250 (0.010)	0.510 (0.020)	0.373 (0.015)	0.627 (0.025)

POPULAR OPTION

AEC-Q200 moisture resistance

Option to order: 0058: Specific production process to withstand 85 °C/85 % RH at Pn/10

ENVIRONMENTAL TEST

TEST	CONDITIONS	VALUES AND DRIFTS ($\Delta R/R \pm \%$)	
		CECC REQUIREMENTS	TYPICAL PERFORMANCE
Overload	6.25 x rated power / 2 s (or 2 UL)	0.05 % Rn ⁽²⁾ + 0.05 Ω	0.01 % Rn ⁽²⁾
Climatic sequences ⁽¹⁾	-55 °C / +155 °C 5 moisture cycles	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.02 % Rn ⁽²⁾
Thermal shock ⁽¹⁾	-55 °C / +155 °C 5 cycles 30 min	0.05 % Rn ⁽²⁾ + 0.05 Ω	0.02 % Rn ⁽²⁾
Load life ⁽¹⁾	+70 °C/Pn 1000 h	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.05 % Rn ⁽²⁾
Resistance to solder heat	+260 °C/ 10 s	0.05 % Rn ⁽²⁾ + 0.05 Ω	0.02 % Rn ⁽²⁾
Moisture resistance ⁽¹⁾	+40 °C / 93 % HR Pn / 10	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.01 % Rn ⁽²⁾
	AEC-Q200 ⁽³⁾ 85 °C / 85 % RH / Pn / 10 1000 h	0.5 % + 0.05 Ω	Max. < 0.3 % + 0.05 Ω
High temperature storage	1000 h at + 155 °C	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.05 % Rn ⁽²⁾
Bending ⁽¹⁾	10 bends / 2 mm / 5 s	0.05 % Rn ⁽²⁾ + 0.05 Ω	0.02 % Rn ⁽²⁾

SPECIFIC CONDITIONS DUE TO TERMINATION TYPE

TEST	CONDITIONS		VALUES AND DRIFTS	
	B; G	N	VISHAY REQUIREMENTS	TYPICAL PERFORMANCE
Solderability	+235 °C/2 s Sn60Pb40 alloy	+245 °C/3 s Sn97Ag3 alloy	VISUAL INSPECTION	
High T° reflow profile	N/A	+255 °C/40 s (on parts)	0.02 % Rn ⁽²⁾ + 0.05 Ω	0.01 % Rn ⁽²⁾ + 0.05 Ω

Notes
⁽¹⁾ Test requiring parts to be mounted on PCB will be performed with the requirement that termination alloy will be the same as solder paste alloy. Gold termination will be tested as B termination

⁽²⁾ Rn: Nominal Resistance
Pn: Nominal Power


⁽³⁾ Option to order: 0058



PACKAGING INFORMATION

SIZE	NUMBER OF PIECES PER PACKAGE		TAPE WIDTH
	WAFFLE PACK (2" x 2")	TAPE AND REEL Min. Max.	
0505	100	100	4000
0603			5000
0805	100		8 mm (0.315")
1206	140		

DERATING CURVE



GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: RV0505E1001DBT0099

R	V	0	5	0	5	E	1	0	0	1	D	B	T	0	0	9	9
GLOBAL MODEL	SIZE	TCR	VALUE	TOLERANCE	TERMINATION	PACKAGING	OPTION										
	0505 0603 0805 1206	E = ± 25 ppm/°C Y = ± 10 ppm/°C	The first 3 digits (2 digits are enough for tolerance G and J) are significant figures and the last digit specifies the number of zeros to follow. R designates decimal point 10R0 = 10 Ω 3901 = 3900 Ω 1004 = 1 MΩ	B = ± 0.1 % D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 %	B: SnPb over nickel barrier N: SnAg over nickel barrier G: gold over nickel barrier	For more information see "Codification of packaging" table	Leave blank if no option										

B: lead bearing version
N and G: lead (Pb)-free / RoHS version

Historical Part Number example: RV 0505 25PPM 1K 0.5 % B TR R1016

PART NUMBER DESCRIPTION (for information only)

RV	0505	25 PPM	1K	0.5 %	B	TR	R1016
MODEL	SIZE	TCR	OHMIC VALUE	TOLERANCE	TERMINATION	PACKAGING	OPTION



CODIFICATION OF PACKAGING	
CODE 18	PACKAGING
WAFFLE PACK	
W	100 min., 1 mult
WA	100 min., 100 mult (available only in size 1206)
PLASTIC TAPE (Standard for all sizes.)	
T	100 min., 1 mult
TA	100 min., 100 mult
TB	250 min., 250 mult
TC	500 min., 500 mult
TD	1000 min., 1000 mult
TE	2500min., 2500 mult
TF	Full tape (quantity depending on size of chips)
PAPER TAPE (Available for 0603, 0805, and 1206. Please consult Vishay Sfernice for other sizes.)	
PT	100 min., 1 mult
PA	100 min., 100 mult
PB	250 min., 250 mult
PC	500 min., 500 mult
PD	1000 min., 1000 mult
PE	2500min., 2500 mult
PF	Full tape (quantity depending on size of chips)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.