


Item no.:	734-533
Product description:	FEMALE CONNECTOR WITH RIGHT ANGLED SOLDER PIN 3 POLE PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING SOLDER PIN 0.9 MM x 0.9 MM WITH CODING FINGERS MATING DIRECTION PARALLEL TO PCB WITH 2 LATCHES



Produkt kann von Bild abweichen / product may differ

Packing unit 200 pieces

RoHS compliant

Product group	3 (Multi Conn. System)
Weight	1.7 g
Color	light gray
No. of connection Points	3
No. of potentials	3
pole count	3
Height	10.5 mm
Height	0.413 in
Width	12 mm
Width	0.472 in
Depth	14.65 mm
Depth	0.577 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	160 V

Measured shock voltage	2.5 kV
Current intensity EN	10 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	10 A



Material group
Customs Tariff No.
Country of Origin

I
85366990
Deutschland



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
734-533	CSA	154112-1465035	150	10	28-14
734-533	UR	E45171	250	10	
734-533	UR	E45172	300	10	

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected