






Amp	Volt	Hz	IP Ident. colour + h	Part No.	Couplers		3 P + N + 	IEC/EN 60 309	 g	EAN-No. 4015609...																															
					couplers, suspension type, gland entry																																				
16	400	50/60	6	314					10 221	000425																															
32	400	50/60	6	334					10 307	000494																															
					<table><tr><th>Ampère</th><th>d</th><th>Øe</th><th>f</th><th>m</th><th>Pg</th></tr><tr><td>16 A</td><td>148</td><td>65</td><td>85</td><td>113</td><td>16</td></tr><tr><td>32 A</td><td>180</td><td>72</td><td>91</td><td>136</td><td>21</td></tr></table>					Ampère	d	Øe	f	m	Pg	16 A	148	65	85	113	16	32 A	180	72	91	136	21														
Ampère	d	Øe	f	m	Pg																																				
16 A	148	65	85	113	16																																				
32 A	180	72	91	136	21																																				
					coupler, suspension type, gland entry for larger conductor sizes																																				
16	400	50/60	6	315					10 224	000432																															
					<table><tr><th>Ampère</th><th>d</th><th>Øe</th><th>f</th><th>m</th><th>Pg</th></tr><tr><td>16 A</td><td>148</td><td>65</td><td>85</td><td>113</td><td>21</td></tr></table>					Ampère	d	Øe	f	m	Pg	16 A	148	65	85	113	21																				
Ampère	d	Øe	f	m	Pg																																				
16 A	148	65	85	113	21																																				
					gland entry																																				
16	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	319 319 504 319 509 319 511					10 252	000449 016549 016563 016570																															
32	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	339 339 504 339 509 339 511					10 346	000500 017447 017461 017478																															
63	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	369 369 504 369 509 369 511					5 844	000531 017997 018017 018024																															
125	400 110 230 440	50/60 50/60 50/60 60	6 4 9 11	379 379 504 379 509 379 511					2 1710	000548 018192 018239 018246																															
with Multi Contact																																									
					<table><tr><th>Ampère</th><th>d</th><th>f</th><th>m</th><th>u</th><th>Pg</th></tr><tr><td>16 A</td><td>143</td><td>91</td><td>126</td><td>88</td><td>16</td></tr><tr><td>32 A</td><td>170</td><td>105</td><td>149</td><td>103</td><td>21</td></tr><tr><td>63 A</td><td>255</td><td>117</td><td>206</td><td>110</td><td>36</td></tr><tr><td>125 A</td><td>332</td><td>130</td><td>275</td><td>130</td><td>48</td></tr></table>					Ampère	d	f	m	u	Pg	16 A	143	91	126	88	16	32 A	170	105	149	103	21	63 A	255	117	206	110	36	125 A	332	130	275	130	48		
Ampère	d	f	m	u	Pg																																				
16 A	143	91	126	88	16																																				
32 A	170	105	149	103	21																																				
63 A	255	117	206	110	36																																				
125 A	332	130	275	130	48																																				