

## Lamp Specification


Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-1680	S-8	BA15s	6V 4.10A	C-6

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
6.0	3.69	4.10	4.51	25.6	32.0	38.4	300 Hrs

### Dimensional Characteristics:

- L.C.L. = 1.25" (31.8mm)
- Base = Nickel-plated Brass Construction.

Industry Standard No. 1680



			Title:	
			<b>S-8 Single Contact Bayonet Base Lamp 6V 4.10A Gas-Filled</b>	
Revision			Notes: Unless otherwise specified, all dimensions are in inches.	Rev: 1
Drawn	06/07/09	CI		
Checked	06/07/09	EB		
Approved	06/08/09	EB		