

**General ordering data**

Order No.	1632320000
Part designation	WTA 2 WDU2.5-10
Version	Modular terminal, accessories, Test adapter
EAN	4008190257347
Qty.	25 pc(s).

Product notes

Note, technical data	Rated current 6 A
----------------------	-------------------

CSA rating data

Voltage (CSA)	300 V
CSA current	6 A

Conductors for clamping (additional connection)

Clamping range, max.	1.5 mm ²
Rated cross-section	1.5 mm ²
Clamping screw	M 2.5

Conductors for clamping (rated connection)

Type of connection	Screw connection
No. of connections	1
Stripping length	6 mm
Solid, min.	0.5 mm ²
Solid, max.	1.5 mm ²
Flexible, min.	1 mm ²
Flexible, max.	1.5 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	1.5 mm ²

Dimensions

Width	5 mm
Height of lowest version	107.6 mm
Length	66.1 mm

Dimensions

Rating data

Rated cross-section	1.5 mm ²
Rated voltage	250 V
Rated current	6 A

Stud connection

Tightening torque range	0.4 Nm
-------------------------	--------

Test adapter

Function	Test adapter
With snap-in pegs	No

Test adapter dimensions

Height with TS 35	107.6 mm
With snap-in pegs	No

Test adapter rated data

Rated voltage	250 V
---------------	-------

UL rating data

Voltage (UL)	300 V
Current (UL)	6 A

Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC002255
eClass 4.1	27-14-11-99
eClass 5.0	27-14-11-45
eClass 5.1	27-14-11-45

Similar products

Order No.	Part designation	Version
1632340000	WTA 2/10 WDU2.5/10	Modular terminal, accessories, Test adapter
1632330000	WTA 2/ZA WDU2.5-10	Modular terminal, accessories, Test adapter