



General ordering data

Order No.	9004070000
Part designation	H1,5/18
Version	Wire-end ferrule, 1.5 mm ²
EAN	4008190105761
Qty.	1000 pc(s).

Technical data

Length	18 mm
Width	2.8 mm
Height	2.8 mm

Product data

Conductor rated cross-section	1.5 mm ²
AWG	16
Total length (L1)	18 mm
Contact surface diameter (D1)	1.7 mm
Metal sleeve thickness (S1)	0.15 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Similar products

Order No.	Part designation	Version
9018910000	H0.25/5	Wire-end ferrule, 0.25 mm ²
0282600000	H0.5/6	Wire-end ferrule, 0.5 mm ²
9004050000	H0,5/10	Wire-end ferrule, 0.5 mm ²
0282700000	H0.75/6	Wire-end ferrule, 0.75 mm ²
0542500000	H0.75/10	Wire-end ferrule, 0.75 mm ²
0372600000	H1,0/6	Wire-end ferrule, 1 mm ²
0282800000	H1,0/10	Wire-end ferrule, 1 mm ²
0372700000	H1,5/7	Wire-end ferrule, 1.5 mm ²

0186500000	H1,5/10	Wire-end ferrule, 1.5 mm ²
9004060000	H1,5/12	Wire-end ferrule, 1.5 mm ²
0373000000	H2,5/7	Wire-end ferrule, 2.5 mm ²
9004080000	H2,5/10	Wire-end ferrule, 2.5 mm ²
0186100000	H2,5/12	Wire-end ferrule, 2.5 mm ²
9004090000	H2,5/18	Wire-end ferrule, 2.5 mm ²
0373100000	H4,0/9	Wire-end ferrule, 4 mm ²
0244100000	H4,0/12	Wire-end ferrule, 4 mm ²
9004100000	H4,0/15	Wire-end ferrule, 4 mm ²
9004110000	H4,0/18	Wire-end ferrule, 4 mm ²
9004120000	H6,0/10	Wire-end ferrule, 6 mm ²
0191900000	H6,0/12	Wire-end ferrule, 6 mm ²
0124700000	H6,0/15	Wire-end ferrule, 6 mm ²
9004130000	H6,0/18	Wire-end ferrule, 6 mm ²