



## Wiha SoftFinish® Handle - Standard Series



### 302 Slotted Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM, hardened, hard chromed.  
Wiha-Chromtop tips. Handle, multi-component, cushion grip.

| Item    | +    | +    | +   | +    | +   | +    | +   | +    | +    | +    |
|---------|------|------|-----|------|-----|------|-----|------|------|------|
| No.     | mm   | Inch | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
| 302 05* | 3.0  | .118 | 100 | 3.9  | 0.5 | .020 | 204 | 8.0  | .06  | 10   |
| 302 10* | 3.5  | .139 | 100 | 3.9  | 0.6 | .024 | 204 | 8.0  | .07  | 10   |
| 302 15* | 4.0  | .157 | 100 | 3.9  | 0.8 | .031 | 211 | 8.3  | .11  | 10   |
| 302 17* | 4.0  | .157 | 150 | 5.9  | 0.8 | .031 | 261 | 10.3 | .12  | 10   |
| 302 18* | 4.5  | .187 | 80  | 3.1  | 0.8 | .031 | 191 | 7.5  | .11  | 10   |
| 302 11* | 4.5  | .187 | 125 | 5.0  | 0.8 | .031 | 236 | 9.3  | .12  | 10   |
| 302 19* | 4.5  | .187 | 150 | 5.9  | 0.8 | .031 | 261 | 10.2 | .12  | 10   |
| 302 20* | 5.5  | .216 | 125 | 5.0  | 1.0 | .039 | 236 | 9.3  | .15  | 10   |
| 302 38* | 5.5  | .216 | 300 | 11.8 | 1.0 | .039 | 411 | 16.1 | .24  | 10   |
| 302 22* | 6.0  | .250 | 100 | 3.9  | 1.2 | .047 | 218 | 8.6  | .17  | 10   |
| 302 23  | 6.5  | .255 | 100 | 3.9  | 1.0 | .039 | 218 | 8.6  | .20  | 10   |
| 302 25  | 6.5  | .255 | 150 | 5.9  | 1.2 | .047 | 268 | 10.6 | .22  | 10   |
| 302 27  | 8.0  | .315 | 150 | 5.9  | 1.2 | .047 | 274 | 10.8 | .29  | 10   |
| 302 30  | 8.0  | .315 | 175 | 7.0  | 1.2 | .047 | 299 | 11.8 | .30  | 10   |
| 302 35  | 10.0 | .393 | 200 | 8.0  | 1.6 | .063 | 324 | 12.8 | .36  | 10   |
| 302 36  | 12.0 | .472 | 250 | 9.8  | 2.0 | .078 | 374 | 14.7 | .52  | 10   |

\*Cabinet Tips



### 302 Stubby Slotted Screwdriver, With Wiha-SoftFinish® Handle

| Item   | +   | +    | +  | +    | +   | +    | +  | +    | +    | +    |
|--------|-----|------|----|------|-----|------|----|------|------|------|
| No.    | mm  | Inch | mm | Inch | mm  | Inch | mm | Inch | lbs. | pkg. |
| 302 39 | 4.0 | .157 | 25 | 1.0  | 0.8 | .031 | 75 | 2.95 | .09  | 10   |
| 302 55 | 5.5 | .216 | 25 | 1.0  | 1.0 | .039 | 75 | 2.95 | .09  | 10   |
| 302 65 | 6.5 | .255 | 25 | 1.0  | 1.2 | .047 | 75 | 2.95 | .10  | 10   |



### 358 Square Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item   | +    | +   | +    | +   | +    | +   | +    | +    | +    | + |
|--------|------|-----|------|-----|------|-----|------|------|------|---|
| No.    | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |   |
| 358 01 | 1    | 100 | 3.9  | 4.5 | 5/32 | 210 | 8.2  | .12  | 10   |   |
| 358 02 | 2    | 150 | 5.9  | 5.0 | 1/4  | 268 | 10.5 | .19  | 10   |   |
| 358 03 | 3    | 150 | 5.9  | 6.0 | 1/4  | 268 | 10.5 | .22  | 10   |   |



### 311 Phillips Screwdriver, With Wiha-SoftFinish® Handle

Round blade, high alloy CVM steel, hardened, hard chromed.  
Wiha-Chromtop tips. Handle, multi-component, cushion grip.

| Item   | +    | +   | +    | +    | +    | +   | +    | +    | +    | + |
|--------|------|-----|------|------|------|-----|------|------|------|---|
| No.    | Size | mm  | Inch | mm   | Inch | mm  | Inch | lbs. | pkg. |   |
| 311 05 | 0    | 60  | 2.4  | 3.0  | .118 | 164 | 6.5  | .06  | 10   |   |
| 311 10 | 1    | 80  | 3.1  | 4.5  | .177 | 191 | 7.5  | .11  | 10   |   |
| 311 12 | 1    | 200 | 8.0  | 4.5  | .177 | 311 | 12.3 | .15  | 10   |   |
| 311 14 | 1    | 300 | 12.0 | 4.5  | .177 | 411 | 16.2 | .18  | 10   |   |
| 311 15 | 2    | 100 | 3.9  | 6.0  | .236 | 218 | 8.6  | .20  | 10   |   |
| 311 17 | 2    | 200 | 8.0  | 6.0  | .236 | 318 | 12.5 | .25  | 10   |   |
| 311 18 | 2    | 300 | 12.0 | 6.0  | .236 | 418 | 16.5 | .30  | 10   |   |
| 311 20 | 3    | 150 | 5.9  | 8.0  | .315 | 274 | 10.8 | .33  | 10   |   |
| 311 25 | 4    | 200 | 8.0  | 10.0 | .393 | 323 | 12.7 | .51  | 10   |   |



### 311 Stubby Phillips Screwdriver, With Wiha-SoftFinish® Handle

| Item   | +    | +  | +    | +   | +    | +  | +    | +    | +    | + |
|--------|------|----|------|-----|------|----|------|------|------|---|
| No.    | Size | mm | Inch | mm  | Inch | mm | Inch | lbs. | pkg. |   |
| 311 35 | 1    | 25 | 1.0  | 4.5 | .177 | 75 | 3.0  | .09  | 10   |   |
| 311 40 | 2    | 25 | 1.0  | 6.0 | .236 | 75 | 3.0  | .10  | 10   |   |



### 313 Pozidriv® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

| Item   | +    | +   | +    | +   | +    | +   | +    | +    | +    | + |
|--------|------|-----|------|-----|------|-----|------|------|------|---|
| No.    | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |   |
| 313 05 | 0    | 60  | 2.4  | 3.0 | .118 | 164 | 6.5  | .06  | 10   |   |
| 313 10 | 1    | 80  | 3.1  | 4.5 | .177 | 191 | 7.5  | .11  | 10   |   |
| 313 12 | 1    | 200 | 8.0  | 4.5 | .177 | 311 | 12.3 | .15  | 10   |   |
| 313 15 | 2    | 100 | 3.9  | 6.0 | .236 | 218 | 8.6  | .20  | 10   |   |
| 313 20 | 3    | 150 | 5.9  | 8.0 | .315 | 274 | 10.8 | .33  | 10   |   |