

Wiha Insulated 3/8" Sockets & Sets



NEW
From Wiha

⚠️ 1000Volt

Inch - 6 & 12 Point

SHOP

314 Insulated 3/8" Drive Sockets - 6 & 12 Point, Insulation according to EN/IEC 60900, DIN 7448 specification, up to 1000 Volt. Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	Inch	lbs.	pkg.
314 25	1/4	.07	1
314 28	9/32	.07	1
314 29	5/16	.07	1
314 30	11/32	.07	1
314 31	3/8	.07	1
314 32	7/16	.07	1
314 33	1/2	.09	1
314 34	9/16	.09	1
314 35	5/8	.10	1
314 36	11/16	.13	1
314 37	3/4	.14	1
314 38	13/16	.16	1
314 39	7/8	.18	1

*Sockets must be used with insulated ratchets & extensions



⚠️ 1000Volt

Metric - 12 Point

SHOP

315 Insulated 3/8" Drive Sockets - 12 Point, Insulation according to VDE, EN/IEC 60900, DIN 7448 specification, up to 1000 Volt. Individually Tested. Chrome-vanadium steel, forged, oil-hardened.

Item No.	mm	lbs.	pkg.
315 06	6	.07	1
315 07	7	.07	1
315 08	8	.07	1
315 09	9	.07	1
315 10	10	.07	1
315 11	11	.08	1
315 12	12	.10	1
315 13	13	.10	1
315 14	14	.10	1
315 15	15	.10	1
315 16	16	.10	1
315 17	17	.11	1
315 18	18	.12	1
315 19	19	.14	1
315 20	20	.15	1
315 21	21	.17	1
315 22	22	.18	1
315 24	24	.26	1

*Sockets must be used with insulated ratchets & extensions



⚠️ 1000Volt

SHOP

314 93 10 Pc. Insulated 3/8" Drive Socket Set - Inch

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 314 93 Set includes the following:

⚡	5/16, 3/8, 7/16, 1/2,
lbs. 2.4	9/16, 5/8, 11/16, 3/4"
	12856 3/8" x 125mm Extension Bar
	12852 3/8" Ratchet - 280mm



⚠️ 1000Volt

SHOP

315 90 10 Pc. Insulated 3/8" Drive Socket Set - Metric

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 315 90 Set includes the following:

⚡	8, 10, 11, 12, 13, 14, 17, 19mm
lbs. 2.41	12856 3/8" x 125mm Extension Bar
	12852 3/8" Ratchet - 280mm



⚠️ 1000Volt

SHOP

314 91 16 Pc. Insulated 3/8" Drive Socket Set - Inch/Metric

CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 314 91 Set includes the following:

⚡	5/16, 3/8, 7/16, 1/2,
lbs. 2.01	9/16, 5/8, 11/16, 3/4"
	8, 10, 11, 12, 13,
	14, 17, 19mm