



Wiha Insulated 3/8" Sockets & Sets



1000Volt



314 95 24 Pc. Insulated 3/8" Drive Socket Set - Inch
CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 314 95 Set includes the following:

1/4, 9/32, 5/16, 11/32, 3/8, 7/16

1/2, 9/16, 5/8, 11/16, 3/4" Sockets

lbs. 12856 3/8" x 125mm Extension Bar

9.07 12857 3/8" x 250mm Extension Bar

12852 3/8" Ratchet - 190mm

15000 Insulated Electrician's Knife - 50mm

Slotted: 3.5, 4.5, 6.5mm

Phillips: 1, 2, 3

32806 6.3" Long Nose Pliers

32818 8.0" Combo Pliers

32832 6.3" Diagonal Cutters

*Sockets must be used with insulated ratchets & extensions



1000Volt



315 92 24 Pc. Insulated 3/8" Drive Socket Set - Metric
CV steel, forged, oil-hardened sockets. Insulated to EN/IEC 60900.

Item No. 315 92 Set includes the following:

6, 7, 8, 9, 10, 11, 12,

13, 14, 17, 19mm Sockets

lbs. 12856 3/8" x 125mm Extension Bar

9.08 12857 3/8" x 250mm Extension Bar

12852 3/8" Ratchet - 190mm

15000 Insulated Electrician's Knife - 50mm

Slotted: 3.5, 4.5, 6.5mm

Phillips: 1, 2, 3

32806 6.3" Long Nose Pliers

32818 8.0" Combo Pliers

32832 6.3" Diagonal Cutters

*Sockets must be used with insulated ratchets & extensions

NEW
From Wiha



1000Volt



128 52 Insulated 3/8" Drive Ratchet, EN/IEC 60900

Chrome-Vanadium steel. Reversible.

Item	OAL		W		
No.	Inch	mm	Inch	lbs.	pkg.
128 52	3/8"	190	7.5	.87	1



1000Volt



128 Insulated 3/8" Extension Bars, EN/IEC 60900

Chrome-Vanadium steel.

Item	OAL		W		
No.	Inch	mm	Inch	lbs.	pkg.
128 56	3/8"	125	4.9	.29	1
128 57	3/8"	250	9.8	.57	1



1000Volt



290 09 Insulated 3/8" Drive T-handle

Insulation according to EN/IEC 60900 specification, up to 1000 Volt Rated. Individually Tested. Blade chrome-vanadium steel, hardened.

Item		OAL	OAL	W	
No.	Inch	mm	Inch	lbs.	pkg.
290 09	3/8	200	7.9"	.55	1

Each tool individually tested to 10,000 volts & certified to 1000 Volt ac or 1500 Volt dc