

Wiha Vinyl Grip Pliers & Cutters

Long Nose Pliers



326 Long Nose Pliers With Cutters DIN ISO 5745

Long nose pliers. Extra long cutters for flat and round cables. Serrated Jaws. Cutting edges additionally induction hardened to approx. 60 HRC. Special CV tool steel forgings. Soft vinyl grips are oil & solvent resistant.

Item No.		mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
326 18	Z05016001	160	6.3	#10	1	.28
326 21	Z05020001	200	8.0	#8	1	.36

Bent Long Nose Pliers

Angled 40°



326 Bent Long Nose Pliers With Cutters DIN ISO 5745

Long nose pliers angled 40°. Extra long cutters for flat and round wire. Partially Serrated Jaws. Cutting edges additionally induction hardened to approx. 60 HRC. Special CV tool steel forgings. Soft vinyl grips are oil & solvent resistant.

Item No.		mm	Inch	Cutting Capacity Copper AWG	Pkg.	wt.
326 23	Z05116001	160	6.3	#10	1	.28
326 25	Z05120001	200	8.0	#8	1	.36

Long Flat Nose Pliers



326 30 Long Flat Nose Pliers DIN ISO 5745

Extra long head. Serrated Jaws are induction hardened. Special CV tool steel forgings. Use for gripping and right-angled bending of wires and sheet metal parts. Soft vinyl grips are oil & solvent resistant.

Item No.		mm	Inch	Pkg.	wt.
326 30	Z07016001	160	6.3	1	.26

Long Round Nose Pliers



326 33 Long Round Nose Pliers DIN ISO 5745

Extra long head. Serrated Jaws are induction hardened. Special CV tool steel forgings. Use for gripping and uniform round bending of wires and sheet metal parts. Soft vinyl grips are oil & solvent resistant.

Item No.		mm	Inch	Pkg.	wt.
326 33	Z09016001	160	6.3	1	.25