

Wiha ComfortGrip Pliers

ComfortGrip Long Nose Pliers



SHOP

329 Long Nose Pliers With Cutting Edge DIN ISO 5745

Long nose pliers. Extra long cutters for flat and round wires. Gripping surfaces serrated in parts. Cutting edges additionally induction hardened to approx. 60 HRC. Special tool steel. Two component ComfortGrip handle.

Item No.		↔ mm	↔ Inch	Cutting Capacity Copper AWG	🔧 Pkg.	📦 wt.
329 19	Z05016005	160	6.3	#10	1	.32
329 22	Z05020005	200	8.0	#8	1	.42

ComfortGrip Bent Long Nose Pliers

Angled approx. 40°



SHOP

329 Bent Nose Pliers With Cutters DIN ISO 5745

Long nose pliers angled approx. 40°. Extra long cutting edge for flat and round wires. Gripping surfaces serrated in parts. Cutting edges additionally induction hardened to approx. 60 HRC. Special tool steel. Two component ComfortGrip handle.

Item No.		↔ mm	↔ Inch	Cutting Capacity Copper AWG	🔧 Pkg.	📦 wt.
329 24	Z05116005	160	6.3	#10	1	.32
329 25	Z05120005	200	8.0	#8	1	.42

ComfortGrip Flat Nose Pliers



SHOP

329 31 Long Flat Nose Pliers DIN ISO 5745

Extra long head. Gripping surfaces serrated and induction hardened. Special tool steel. Two component ComfortGrip handle. Gripping and right-angled bending of wires and sheet metal parts.

Item No.		↔ mm	↔ Inch	Cutting Capacity Copper AWG	🔧 Pkg.	📦 wt.
329 31	Z07016005	160	6.3	#6	1	.32

ComfortGrip Diagonal Cutters



SHOP

329 Diagonal Cutters DIN ISO 5749

Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edge is achieved with additional induction hardening to approx. 60 HRC. Special CV tool steel forgings hardened and tempered. For soft & medium hard wire.

Item No.		↔ mm	↔ Inch	Cutting Capacity Copper AWG	🔧 Pkg.	📦 wt.
329 36	Z12014005	140	5.5	#6	1	.39
329 40	Z12016005	160	6.3	#6	1	.48
329 43	Z12018005	180	7.0	#6	1	.62

ComfortGrip High Leverage Diagonal Cutters



SHOP

329 High Leverage Diagonal Cutters DIN ISO 5749

Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Low force action, clean cutting. Long life cutting edges are achieved through additional induction hardening to approx. 64 HRC. C60 special CV tool steel hardened and tempered.

Item No.		↔ mm	↔ Inch	Cutting Capacity Copper AWG	🔧 Pkg.	📦 wt.
329 49	Z16016005	160	6.3	#6	1	.48
329 50	Z16018005	180	7.0	#5	1	.57
329 53	Z16020005	200	8.0	#4	1	.64