

## Wiha Insulated T-handles

### Insulation Test Standards:

Insulation according to EN/IEC 60900,  
ASTM F-1505-01, New VDE 0682/part 201,  
DIN 7437, NFPA70E


Responds to OSHA's use  
specification 29 CFR1910

Each tool individually  
tested to 10,000 volts  
and certified to 1000  
Volt ac or 1500 Volt dc

**Insulation**  
molded directly onto blade  
for permanent bonding

**Blade**  
CVM tool steel, hardened  
to average 58/60RC

 **1000V**



 **1000Volt**


[SHOP](#)

**334** Inch T-handle, With Wiha-Molded Handle Insulation According  
to ASTM F-1505-01, New VDE Specification 0682/part 201 and  
EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested.

Blade CVM steel, hardened. Insulation molded directly onto blade.

Wiha-SoftFinish® handle, multi-component.

| Item          |  |  |  |  |  |  |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| No.           | Inch                                                                                | Inch                                                                                | Inch                                                                                | mm                                                                                  | lbs.                                                                                | pkg.                                                                                |
| <b>334 81</b> | 5/32                                                                                | 5.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .09                                                                                 | 10                                                                                  |
| <b>334 82</b> | 3/16                                                                                | 5.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .15                                                                                 | 10                                                                                  |
| <b>334 83</b> | 7/32                                                                                | 5.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .19                                                                                 | 10                                                                                  |
| <b>334 85</b> | 1/4                                                                                 | 6.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .20                                                                                 | 10                                                                                  |
| <b>334 86</b> | 5/16                                                                                | 6.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .26                                                                                 | 10                                                                                  |
| <b>334 87</b> | 3/8                                                                                 | 6.9                                                                                 | 6.9                                                                                 | 176                                                                                 | .44                                                                                 | 10                                                                                  |



 **1000Volt**

[SHOP](#)

**334** Metric T-handle, With Wiha-Molded Handle Insulation  
According to ASTM F-1505-01, New VDE Specification 0682/part 201  
and EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested.

Blade CVM steel, hardened. Insulation molded directly onto blade.

Wiha-SoftFinish® handle, multi-component.

| Item          |  |  |  |  |  |  |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| No.           | mm                                                                                  | mm                                                                                  | Inch                                                                                | mm                                                                                  | Inch                                                                                | lbs.                                                                                |
| <b>334 41</b> | 4.0                                                                                 | 150                                                                                 | 5.9                                                                                 | 176                                                                                 | 6.9                                                                                 | .09                                                                                 |
| <b>334 43</b> | 5.0                                                                                 | 150                                                                                 | 5.9                                                                                 | 176                                                                                 | 6.9                                                                                 | .15                                                                                 |
| <b>334 45</b> | 6.0                                                                                 | 150                                                                                 | 5.9                                                                                 | 176                                                                                 | 6.9                                                                                 | .18                                                                                 |
| <b>334 47</b> | 8.0                                                                                 | 150                                                                                 | 5.9                                                                                 | 176                                                                                 | 6.9                                                                                 | .26                                                                                 |

[PREVIOUS](#)



 **1000Volt**

[SHOP](#)

**334 90** Set 6 Pcs. Inch T-handle Hex

| Item          |  |  |  |  |  |  |
|---------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| No.           | Inch                                                                                  | Inch                                                                                  | Inch                                                                                  | Inch                                                                                  | Inch                                                                                  | lbs.                                                                                  |
| <b>334 90</b> | 334 81                                                                                | 5/32                                                                                  | 6.9                                                                                   | 334 85                                                                                | 1/4                                                                                   | 6.9                                                                                   |
|               | 334 82                                                                                | 3/16                                                                                  | 6.9                                                                                   | 334 86                                                                                | 5/16                                                                                  | 6.9                                                                                   |
|               | 334 83                                                                                | 7/32                                                                                  | 6.9                                                                                   | 334 87                                                                                | 3/8                                                                                   | 6.9                                                                                   |



 **1000Volt**

[SHOP](#)

**334 91** Set 4 Pcs. Metric T-handle Hex

| Item          |  |  |  |  |  |  |
|---------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| No.           | mm                                                                                    | mm                                                                                    | mm                                                                                    | mm                                                                                    | mm                                                                                    | .99 lbs.                                                                              |
| <b>334 91</b> | 334 41                                                                                | 4.0                                                                                   | 150                                                                                   | 334 45                                                                                | 6.0                                                                                   | 150                                                                                   |
|               | 334 43                                                                                | 5.0                                                                                   | 150                                                                                   | 334 47                                                                                | 8.0                                                                                   | 150                                                                                   |

[NEXT](#)