



Wiha **TORX**® PocketStar



Push button
key release



363 96 **TORX**® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

Item No.

363 96 PocketStar lbs. .22

TORX®: T7, T8, T9, T10, T15, T20, T25

Blade length range 1.68 - 1.94"



Push button
key release



363 98 **TORX**® PocketStar Fold Outs, 8 Pc. Set


High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

Item No.

363 98 PocketStar lbs. .24

TORX®: T9, T10, T15, T20, T25, T27, T30, T40

Blade length range 1.95 - 2.39"



PREVIOUS

Wiha Security **TORX**® PocketStar



Push button
key release



363 95 Tamper Resistant **TORX**® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

Item No.

363 95 PocketStar lbs. .22

TR TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s

Blade length range 1.68 - 1.94"



Push button
key release



363 97 Tamper Resistant **TORX**® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

Item No.

363 97 PocketStar lbs. .24

TR TORX®: T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Blade length range 1.95 - 2.39"



Push button
key release



366 97 **TORXPlus**® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle.

Item No.

366 97 PocketStar lbs. .31

TORXPlus®: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25

NEXT