

Wiha 1/4" Socket Accessories


[SHOP](#)

601 45 1/4" Reversible Ratchet Varicat - 32 Tooth

DIN 3122 D - ISO 3315

Forged body, satin finish, nickel and hard chrome.

Item			
No.	Inch	mm	wt.
601 45	5.5	140	.18


[SHOP](#)

601 46 1/4" Reversing Ratchet - 20 Tooth, Push Through Type

20 tooth ratchet. DIN 3122 C - ISO 3315

Forged ratchet body, satin finish, nickel and hard chrome.

Item			
No.	Inch	mm	wt.
601 46	6.0	150	.18


[SHOP](#)

601 31 1/4" Sliding T-handle

DIN 3122 A - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.


Item			
No.	Inch	mm	wt.
601 31	4.5	114	.09


[SHOP](#)

601 1/4" Extension Bar

DIN 3123 B - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	w
601 32	2.17	50	.0
601 33	3.93	100	.1
601 34	5.90	150	.1


[SHOP](#)

601 35 1/4" Wobble Extension Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 35	3.93	100	.10


[SHOP](#)

601 36 1/4" Universal Joint Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 36	1.4	35	.05


[SHOP](#)

601 37 1/4" Swivel Handle Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt
601 37	6.10	155	.25


[SHOP](#)

601 38 1/4" Spinner Handle Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt
601 38	6.10	155	.25


[SHOP](#)

601 39 1/4" Flexible Extension Hard chrome finish.

Item			
No.	Inch	mm	wt
601 39	4.72	120	.11


[SHOP](#)

601 40 1/4" Converter To 3/8" Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 40	1.06	27	.04


[SHOP](#)

601 41 1/4" Square Coupler Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
601 41	.79	20	.01