Wiha 3/8" Socket Accessories

SHOP

602 65 **3/8" Reversible Ratchet**

45 tooth ratchet. DIN 3122 D - ISO 3315

hard chrome finish, polished head.

Item No.	Inch	mm	wt.
602 65	7.8	198	.63

SHOP

602 66 **3/8" Reversible Ratchet Varicat**

32 tooth ratchet. DIN 3122 D - ISO 3315

Forged ratchet body, satin finish, nickel and hard chrome finish.

Spring-loaded retaining ball.

Item No.	Inch	mm	wt.
602 66	7.9	200	.54

SHOP

602 67 **3/8" Ratchet Push-Thru Type**

30 tooth. DIN 3122 C - ISO 3315

hard chrome finish, polished head.

Item No.	Inch	mm	wt.
602 67	7.9	200	.54

SHOP

602 68 **3/8" Flexible Head Reversible Ratchet**

60 tooth ratchet.

hard chrome finish, polished head.

Item No.	Inch	mm	wt.
602 68	10.04	255	.73

Provides ratcheting feature for non ratcheting tools. Use with, extension bars, speed brace, sliding T-handle and swivel handle.

602 49 **3/8" Reversible Ratchet Unit**

SHOP

60 tooth ratchet. DIN 3122 A - ISO 3315

Hard chrome finish, satin finish with spring-loaded retaining ball.

Item No.	Inch	mm	wt.
602 49	1.97	50	.44

602 **3/8" Extension Bar**

SHOP

DIN 3123 B - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item No.	Inch	mm	wt.
602 52	2.95	75	.14
602 51	4.92	125	.20
602 55	9.84	250	.36

602 **3/8" Wobble Extension** Hard chrome finish, fully polished with spring-loaded retaining ball.

SHOP

Item No.	Inch	mm	wt.
602 53	2.95	75	.13
602 54	5.91	150	.23
602 56	9.84	250	.36

SHOP

602 48 **3/8" Speed Brace**

DIN 3122 B - ISO 3315

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item No.	Inch	mm	wt.
602 48	11.97	304	.57

SHOP

602 50 **3/8" Sliding T-handle**

DIN 3122 A - ISO 3315

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item No.	Inch	mm	wt.
602 50	7.9	200	.35