




Metric Ball End Hex Keys Chrome Finish



669 Ball End Metric Hex L-Key, Long

Blade CVM steel, hardened, hard chrome finish.

Item No.	mm	mm	mm	lbs.	pkg.
669 04	1.5	90	14	.004	10
669 08	2.0	99	16	.007	10
669 12	2.5	111	18	.012	10
669 18	3.0	125	20	.019	10
669 22	4.0	138	25	.042	10
669 26	5.0	158	28	.072	10
669 30	6.0	178	32	.12	10
669 37	8.0	198	36	.23	10
669 38	10.0	221	40	.40	10



669 94 9 Pc. Metric Ball End Long Hex L-Key Set

Blade CVM steel, hardened, hard chrome finish. In plastic holder.

Item No.	mm	mm	mm	mm	lbs.
669 94	669 04	1.5	90	669 26	5.0 158 .98
	669 08	2.0	99	669 30	6.0 178
	669 12	2.5	111	669 37	8.0 198
	669 18	3.0	125	669 38	10.0 221
	669 22	4.0	138		




669 95 Set 6 Pc. Metric Ball End Long Hex L-Key Set

Blade CVM steel, hardened, hard chrome finish In Plastic Holder.

Item No.	mm	mm	mm	mm	lbs.
669 95	669 04	1.5	90	669 18	3.0 125 .21
	669 08	2.0	99	669 22	4.0 138
	669 12	2.5	111	669 26	5.0 158

Inch Ball End Hex Keys Chrome Finish



369 Ball End Inch Hex L-Key, Long Arm

Blade CVM steel, hardened, hard chrome finish.

Item No.	Inch	Inch	Inch	lbs.	pkg.
369 40	.050	2.8	.5	.002	10
369 41	1/16	3.1	.6	.004	10
369 42	5/64	3.5	.7	.007	10
369 43	3/32	3.9	.7	.010	10
369 48	7/64	4.3	.7	.016	10
369 49	1/8	4.6	.8	.021	10
369 51	9/64	5.2	.9	.029	10
369 54	5/32	5.7	1.0	.035	10
369 57	3/16	6.2	1.1	.059	10
369 58	7/32	6.7	1.2	.092	10
369 60	1/4	7.3	1.2	.13	10
369 61	5/16	8.0	1.4	.22	10
369 63	3/8	8.8	1.6	.36	10



369 98 13 Pc. Inch Ball End Long Hex L-Key Set in Plastic Holder

Blade CVM steel, hardened, hard chrome finish.

Item No.	Inch	Inch	Inch	Inch	lbs.
369 98	369 40	.050	2.8	369 54	5/32 5.7 1.0
	369 41	1/16	3.1	369 57	3/16 6.2
	369 42	5/64	3.5	369 58	7/32 6.7
	369 43	3/32	3.9	369 60	1/4 7.3
	369 48	7/64	4.3	369 61	5/16 8.0
	369 49	1/8	4.6	369 63	3/8 8.8
	369 51	9/64	5.2		



669 93 2 Pack Inch & Metric Ball End Hex L-key Sets High alloy CVM steel, hardened, hard chrome finish. In plastic Holders.

Item No	lbs.
669 93 2 Sets with 22 L-keys include:	
Sizes - 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm	2.12
Sizes - .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	