


Dura Torsion Insert and Power Bits

With the Dura bit Wiha has again proved it's power of innovation. The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.



Torsion Zone

Positive location in the screw head with decrease of:

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect

Carbide Coated



[SHOP](#)

711 Dura Bits, Phillips, 1/4"

Item No.	Size	mm	lbs.	Each Bit
711 11	1	25	.02	\$4.66
711 12	2	25	.02	\$4.66
711 13	3	25	.02	\$4.66



[SHOP](#)

712 Dura Bits, Pozidriv, 1/4"

Item No.	Size	mm	lbs.	Each Bit
712 11	1	25	.02	\$4.52
712 12	2	25	.02	\$4.52
712 13	3	25	.02	\$4.52



[SHOP](#)

741 Dura Phillips Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.	Each Bit
741 41	1	50	.04	\$6.34
741 42	2	50	.04	\$6.34
741 43	3	50	.04	\$6.34



[SHOP](#)

742 Dura Pozidriv Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.	Each Bit
742 41	1	50	.04	\$6.16
742 42	2	50	.04	\$6.16
742 43	3	50	.04	\$6.16



[SHOP](#)

710 Dura Bits, Slotted, 1/4"

Item No.	mm	Inch	mm	Inch	mm	Each Bit
710 10	0.6	.024	4.5	.177	25	\$5.48
710 11	0.8	.030	5.5	.216	25	\$5.48
710 12	1.0	.039	5.5	.216	25	\$5.48
710 13	1.2	.039	6.5	.255	25	\$5.48




[SHOP](#)

715 Dura Bits, TORX, 1/4"

Item No.	Size	mm	lbs.	Each Bit
715 74	T10	25	.02	\$7.12
715 76	T15	25	.02	\$7.12
715 78	T20	25	.02	\$7.12
715 80	T25	25	.02	\$7.12
715 82	T30	25	.02	\$7.12
715 84	T40	25	.03	\$7.12

Diamond Torsion Insert and Power Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.



Torsion Zone

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

Reduction of:

- pressure forces to be applied
- wear and tear of bit and screw head
- working time
- working costs
- Cam-out effect

The ideal bit even for the most difficult of applications



[SHOP](#)

710 Diamond Bits, Slotted, 1/4"

Item No.	mm	Inch	mm	Inch	mm	Each Bit
710 20	4.5	.177	0.6	.024	25	\$5.16
710 21	5.5	.216	0.8	.030	25	\$5.16
710 22	5.5	.216	1.0	.039	25	\$5.16
710 23	6.5	.255	1.2	.039	25	\$5.16
710 24	8.0	.315	1.2	.063	25	\$5.16



[SHOP](#)

711 Diamond Bits, Phillips, 1/4"

Item No.	Size	mm	lbs.	Each Bit
711 81	1	25	.02	\$4.48
711 82	2	25	.02	\$4.48
711 83	3	25	.02	\$4.48



[SHOP](#)

712 Diamond Bits, Pozidriv, 1/4"

Item No.	Size	mm	lbs.	Each Bit
712 21	1	25	.02	\$4.36
712 22	2	25	.02	\$4.36
712 23	3	25	.02	\$4.36

Diamond Coated



[SHOP](#)

715 Diamond Bits, TORX, 1/4"

Item No.	Size	mm	lbs.	Each Bit
715 16	T10	25	.02	\$6.54
715 17	T15	25	.02	\$6.54
715 18	T20	25	.02	\$6.54
715 19	T25	25	.02	\$6.54
715 21	T30	25	.02	\$6.54
715 22	T40	25	.03	\$6.54



[SHOP](#)

741 Diamond Phillips Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item No.	Size	mm	lbs.	Each Bit
741 61	1	50	.03	\$5.98
741 62	2	50	.03	\$5.98
741 63	3	50	.04	\$5.98