







T-1 3/4 Super Bright LED Lamps

**351-5100, 351-5300,
351-5200, 351-5500**



Dimensions: (In.)

Specifications (Ta= 25°C):

- Type: T-1 3/4 super bright LED
- Reverse current @5V: 10μA
- Operating temperature range: -40°~+85°C
- Storage temperature: -40°~+100°C
- Lead solder temperature (.079" below case): 260°C for 5 seconds max.
- Light color: red (351-5100, 351-5200), yellow (351-5300), green (351-5500)
- Lens color: water clear
- Viewing angle: 20°

(Ta=25°C)

Mouser Stock No.	Dice Material	Forward Voltage (V) @ I=20mA		Peak Wavelength (nm)	Power Dissipation max. (mW)	DC Forward Current max. (mA)	Peak Forward Current Max.	Luminous Intensity(mcd) @ 20mA	
		typ.	max.					min.	typ.
351-5100	GaAlAs	1.5	2.4	660	100	30	100	550	900
351-5200	GaAlAs	1.5	2.4	660	80	40	120	1100	1800
351-5300	AlGaInP	1.7	2.6	590	75	30	60	900	2200
351-5500	GaP	1.7	2.6	565	100	30	120	350	550



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[351-5100](#) [351-5300](#) [351-5200](#)