


DIMENSIONS: mm (In.)



■ **Specifications for Primary:**

- Input Voltage 120VAC, 60Hz
- DC Resistance +/- 15%: 270 OHM

■ **Specifications for Secondary Output:**

- Open Circuit Voltage +/- 5%: 7.2VAC
- Loaded Voltage +/- 5%: 5VAC@500mA

■ **Features:**

- Insulation Resistance:
 - PRI Winding SEC Winding - 100M ohm, 500VDC
- Dielectric Strength:
 - PRI Winding SEC Winding - 1500VAC@2mA 1Minute
 - PRI Winding CORE: 1500VAC@2mA 1Minute
 - SEC Winding CORE: 500VAC@2mA 1Minute

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-205054](#)