











3M™ Ribbon Cable Socket 2 mm X 2 mm Pitch 158 Series




PERFORMANCE [7][8]	
CURRENT:	1A, 6 LINES ENERGIZED
INSULATION RESISTANCE:	>1X10 ⁹ OHMS AT 500 VDC
WITHSTANDING VOLTAGE:	500 VACrms AT SEA LEVEL
TEMPERATURE RATING:	-55°C TO +105°C

- NOTES
- MATERIAL:
BODY: HIGH TEMP GLASS
FILLED POLYESTER,
GRAY UL94V-0
CONTACTS: COPPER ALLOY
 - PLATING:
2.03-3.81 μ m [80-150 μ in]
NICKEL UNDERPLATE
0.38 μ m [15 μ in] OR
0.76 μ m [30 μ in] AVG
GOLD ON WIPING AREA.
 - RIBBON CABLE:
RECOMMENDED: 3M™ 3625
(28 AWG, 7 STRAND).
 - APPLICATION TOOLS:
3460 PRESS (OR EQUIVALENT)
3443-119 LOCATOR PLATE,
3442-9 PLATEN
SEE 3M INSTRUCTION SHEET
78-9101-2810-3.
 - MATES WITH 3M™ HEADERS
159 SERIES (REFERENCE 3M
DRAWING 78-5100-2359-7).
(0.51 mm [0.020 in] SQ,
CROWNED PINS).
 - SEE THE REGULATORY
INFORMATION APPENDIX (RIA)
IN THE "RoHS COMPLIANCE"
SECTION OF
WWW.3MCONNECTOR.COM FOR
COMPLIANCE INFORMATION
(RIA E1 & C1 APPLY).
 - FOR PRODUCT SPECIFICATIONS
AND WARRANTY INFORMATION
SEE 3M 78-5102-0078-1.
 - IN THE EVENT OF CONFLICT
BETWEEN THIS DATA AND
THAT CONTAINED IN THE
PRODUCT SPECIFICATION,
THE PRODUCT SPECIFICATION
TAKES PRECEDENT.


B 31126				NOV 11, 2010				LDS		SF	
				ADDED DIMENSIONS							
				REVISED ORDERING INFORMATION							
A 30741				OCT 28, 2010				LDS		SF	
				INITIAL RELEASE							
DESIGN REFERENCE				NEXT ASSEMBLY							
DISTRIBUTION CODES				REV ECO				ISSUE DATE AND DESCRIPTION			
DRFT L. SCHMIDT				DATE JUL 23, 2010				MFG DATE			
CHKD				DATE				APPR. S. FELDMAN			
								DATE JUL 30, 2010			
DIVISION				DIVISION CODE							
DO NOT SCALE DRAWING				SCALE 6 1				TOLERANCES EXCEPT AS NOTED			
				INCHES 0 ± 0.00 ± 0.005 ± 0.000 ±				THIRD ANGLE PROJECTION			
THIRD ANGLE PROJECTION ASME Y14.5 - 1994				MILLIMETERS 0 ± 0.00 ± 0.005 ± 0.000 ±							
MAX SURFACE ROUGHNESS 125 ✓ X MARKED ONLY				□ ALL SURFACES ± .13 ANGLES ± 1°							
3M				3M Center St. Paul, MN 55144				© 3M COPYRIGHT 2010 This document and information it contains are the property of 3M and are not to be reproduced, distributed, or used in any manner without the prior written permission of 3M. All rights reserved.			
TITLE				3M RIBBON CABLE SOCKET 2 MM x 2 MM PITCH 158 SERIES							
CAGE NUMBER				SIZE				DRAWING NO.			
D				78-5100-2358-9				REV. B			
MODEL				DET. LISTS				YES X NO			
				SHT 1				OF 2			

3M™ Ribbon Cable Socket 2 mm X 2 mm Pitch 158 Series


NUMBER OF POSITIONS	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G
6	6.39 [.252]	12.64 [.497]	8.98 [.354]	10.81 [.426]	11.32 [.446]	12.64 [.497]	N/A
8	8.39 [.330]	14.64 [.576]	10.98 [.432]	12.81 [.504]	13.32 [.524]	14.64 [.576]	N/A
10	10.39 [.409]	16.64 [.655]	12.98 [.511]	14.81 [.583]	15.32 [.603]	16.64 [.655]	N/A
12	12.39 [.488]	18.64 [.734]	14.98 [.590]	16.81 [.662]	17.32 [.682]	18.64 [.734]	N/A
14	14.39 [.567]	20.64 [.812]	16.98 [.669]	18.81 [.741]	19.32 [.761]	20.64 [.812]	8.00 [.315]
16	16.39 [.645]	22.64 [.891]	18.98 [.747]	20.81 [.819]	21.32 [.839]	22.64 [.891]	10.00 [.394]
20	20.39 [.803]	26.64 [1.049]	22.98 [.905]	24.81 [.977]	25.32 [.997]	26.64 [1.049]	14.00 [.551]
22	22.39 [.882]	28.64 [1.127]	24.98 [.984]	26.81 [1.056]	27.32 [1.076]	28.64 [1.127]	16.00 [.630]
24	24.39 [.960]	30.64 [1.206]	26.98 [1.062]	28.81 [1.134]	29.32 [1.154]	30.64 [1.206]	18.00 [.709]
26	26.39 [1.039]	32.64 [1.285]	28.98 [1.141]	30.81 [1.213]	31.32 [1.233]	32.64 [1.285]	20.00 [.787]
30	30.39 [1.197]	36.64 [1.442]	32.98 [1.299]	34.81 [1.371]	35.32 [1.391]	36.64 [1.442]	24.00 [.945]
34	34.39 [1.354]	40.64 [1.600]	36.98 [1.456]	38.81 [1.528]	39.32 [1.548]	40.64 [1.600]	28.00 [1.102]
40	40.39 [1.590]	46.64 [1.836]	42.98 [1.692]	44.81 [1.764]	45.32 [1.784]	46.64 [1.836]	34.00 [1.339]
44	44.39 [1.748]	50.64 [1.994]	46.98 [1.850]	48.81 [1.922]	49.32 [1.942]	50.64 [1.994]	38.00 [1.496]
50	50.39 [1.984]	56.64 [2.230]	52.98 [2.086]	54.81 [2.158]	55.32 [2.178]	56.64 [2.230]	44.00 [1.732]




SOCKET WITHOUT OPTIONS
ALL POSITIONS



CENTER BUMP OPTION
ALL POSITIONS



CENTER BUMP WITH
FRICTION BUMP OPTION
14-50 POSITIONS




CENTER FRICTION BUMP OPTION
6-12 POSITIONS ONLY

ORDERING INFORMATION

TIER 1 - BEST
1581XX-1X00
TIER 1 = BEST
POSITION COUNT (SEE TABLE)
PART CONFIGURATION
1 = ADHESIVE COVER
POLARIZATION/LATCHING
1 = CENTER BUMP,
NO FRICTION BUMP
PLATING
BLANK = 0.76 μ m
[30 μ in] GOLD
PACKAGING
0 = TRAY

TIER 2 - BETTER
1582XX-0X20XX
TIER 2 = BETTER
POSITION COUNT (SEE TABLE)
PART CONFIGURATION
0 = PREASSEMBLED COVER
POLARIZATION/LATCHING
0 = WITHOUT CENTER BUMP
1 = CENTER BUMP,
NO FRICTION BUMP
2 = CENTER BUMP AND
FRICTION BUMP
PLATING
BLANK = 0.76 μ m
[30 μ in] GOLD
15 = 0.38 μ m
[15 μ in] GOLD
PACKAGING
2 = SWORDS

TIER 3 - VALUE
1583XX-211015
TIER 3 = VALUE
POSITION COUNT (SEE TABLE)
PART CONFIGURATION
2 = SEPARATE COVER
POLARIZATION/LATCHING
1 = CENTER BUMP,
NO FRICTION BUMP
PLATING
15 = 0.38 μ m
[15 μ in] GOLD
PACKAGING
1 = BULK PACK



STRAIN RELIEF
3448-158XX
POSITION COUNT
(SEE TABLE)

METRIC [ENGLISH]

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
1581XX-1X00		L. SCHMIDT		JUL 23, 2010		
DIVISION	DIVISION CODE	CHKD		DATE	APPR	DATE
					S. FELDMAN	JUL 30, 2010
DO NOT SCALE DRAWING	SCALE 6-1	TOLERANCES EXCEPT AS NOTED	INCHES			
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5 - 1994	MAX SURFACE ROUGHNESS	MILLIMETERS			
125		ALL SURFACES MARKED ONLY	0 ±			
			.00 ± .13			
			.000 ±			
			ANGLES ±1°			
TITLE			3M RIBBON CABLE SOCKET 2 MM x 2 MM PITCH 158 SERIES			
CAGE NUMBER			DRAWING NO.		REV.	
125			D78-5100-2358-9		B	
MODEL			DET		SHT 2 OF 2	