




3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS





NOTES:

1. MATERIALS:
- | | | |
|--------------|---------------|---------------|
| SPRINGS | SS | |
| CONTACTS | Be Cu | PLATING : Au |
| IC GUIDES | PES | COLOR : BLACK |
| PRESSURE PAD | PES | COLOR : BLACK |
| COVER | PPS or equiv. | COLOR : BLACK |
| BASE | PES | COLOR : BLACK |
2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).
3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE: WWW.3MCONNECTOR.COM PN 248-5205-00

				A		37213		INITIAL RELEASE				ARM											
DESIGN REFERENCE				NEXT ASSEMBLY				REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT		CHKD					
DISTRIBUTION CODES								DRFT		DATE				MFG		DATE							
								CHKD		DATE				APPVL		DATE							
DIVISION				DIVISION CODE				3M 3M Center St. Paul, MN 55144				© 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.											
DO NOT SCALE DRAWING				SCALE 5 1																TOLERANCES EXCEPT AS NOTED			
THIRD ANGLE PROJECTION				INCHES				TITLE QFN TEST SOCKET, 0.5mm 48 pos, EVEN ROW, 7x7 PKG NO TP															
				.01 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002																			
INTERPRET PER ASME Y14.5 - 1994				MILLIMETERS				CAGE NUMBER SIZE DRAWING NO. REV. 78-5100-2471-0 A															
				0 ± .01 ± .00 ± .000 ±																			
MAX SURFACE ROUGHNESS				125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY				MODEL				TEXTTOOL - QFN				DET. LISTS ☐ YES ☒ NO				SHT 1 OF 2			
								ANGLES ± 1°															

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT	DATE			MFG	DATE		
								CHKD	DATE			APPVL	DATE		
DIVISION				DIVISION CODE				3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED											
				INCHES				TITLE QFN TEST SOCKET, 0.5mm 48 pos, EVEN ROW, 7x7 PKG NO TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION				MILLIMETERS				CAGE NUMBER SIZE DRAWING NO. REV.							
INTERPRET PER ASME Y14.5 - 1994				0 ± .1 .0 ± .02 .00 ± .005 0.00 ± .0002											
MAX SURFACE ROUGHNESS 125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY				ANGLES ± 1°				CAGE NUMBER SIZE DRAWING NO. REV.				DET. LISTS ☐ YES ☒ NO			
								MODEL TEXTTOOL - QFN				SHT 2 OF 2			