

## Series AM5T-VZ

### 5 Watt | DC-DC Converter



#### FEATURES:

- Wide 2:1 input range
- 24 Pin DIP Package
- Metal package
- High efficiency up to 80%
- Operating temperature -40°C to + 85°C
- Input / Output isolation 1500 & 3500 VDC
- Pin compatible with multiple manufacturers
- Continuous short circuit protection



#### Models

##### Single output

| Model            | Input Voltage (V) | Output Voltage (V) | Output Current max (mA) | Max. Capacitive load (μF) | Efficiency (%) |
|------------------|-------------------|--------------------|-------------------------|---------------------------|----------------|
| AM5T-1205S-VZ    | 9-18              | 5                  | 1000                    | 2200                      | 74             |
| AM5T-1209S-VZ    | 9-18              | 9                  | 555                     | 470                       | 77             |
| AM5T-1212S-VZ    | 9-18              | 12                 | 416                     | 470                       | 78             |
| AM5T-1215S-VZ    | 9-18              | 15                 | 333                     | 470                       | 78             |
| AM5T-1224S-VZ    | 9-18              | 24                 | 208                     | 220                       | 75             |
| AM5T-2405S-VZ    | 18-36             | 5                  | 1000                    | 2200                      | 75             |
| AM5T-2409S-VZ    | 18-36             | 9                  | 555                     | 470                       | 76             |
| AM5T-2412S-VZ    | 18-36             | 12                 | 416                     | 470                       | 77             |
| AM5T-2415S-VZ    | 18-36             | 15                 | 333                     | 470                       | 78             |
| AM5T-2424S-VZ    | 18-36             | 24                 | 208                     | 220                       | 76             |
| AM5T-4805S-VZ    | 36-72             | 5                  | 1000                    | 2200                      | 77             |
| AM5T-4809S-VZ    | 36-72             | 9                  | 555                     | 470                       | 78             |
| AM5T-4812S-VZ    | 36-72             | 12                 | 416                     | 470                       | 80             |
| AM5T-4815S-VZ    | 36-72             | 15                 | 333                     | 470                       | 80             |
| AM5T-4824S-VZ    | 36-72             | 24                 | 208                     | 220                       | 77             |
| AM5T-1205SH35-VZ | 9-18              | 5                  | 1000                    | 2200                      | 74             |
| AM5T-1209SH35-VZ | 9-18              | 9                  | 555                     | 470                       | 77             |
| AM5T-1212SH35-VZ | 9-18              | 12                 | 416                     | 470                       | 78             |
| AM5T-1215SH35-VZ | 9-18              | 15                 | 333                     | 470                       | 78             |
| AM5T-1224SH35-VZ | 9-18              | 24                 | 208                     | 220                       | 75             |
| AM5T-2405SH35-VZ | 18-36             | 5                  | 1000                    | 2200                      | 75             |
| AM5T-2409SH35-VZ | 18-36             | 9                  | 555                     | 470                       | 76             |
| AM5T-2412SH35-VZ | 18-36             | 12                 | 416                     | 470                       | 77             |
| AM5T-2415SH35-VZ | 18-36             | 15                 | 333                     | 470                       | 78             |
| AM5T-2424SH35-VZ | 18-36             | 24                 | 208                     | 220                       | 76             |
| AM5T-4805SH35-VZ | 36-72             | 5                  | 1000                    | 2200                      | 77             |
| AM5T-4809SH35-VZ | 36-72             | 9                  | 555                     | 470                       | 78             |
| AM5T-4812SH35-VZ | 36-72             | 12                 | 416                     | 470                       | 80             |
| AM5T-4815SH35-VZ | 36-72             | 15                 | 333                     | 470                       | 80             |
| AM5T-4824SH35-VZ | 36-72             | 24                 | 208                     | 220                       | 77             |

#### Models

##### Dual output

| Model         | Input Voltage (V) | Output Voltage (V) | Output Current max (mA) | Max. Capacitive load (μF) | Efficiency (%) |
|---------------|-------------------|--------------------|-------------------------|---------------------------|----------------|
| AM5T-1205D-VZ | 9-18              | ±5                 | ±500                    | ±1000                     | 72             |
| AM5T-1209D-VZ | 9-18              | ±9                 | ±277                    | ±220                      | 76             |
| AM5T-1212D-VZ | 9-18              | ±12                | ±208                    | ±220                      | 77             |
| AM5T-1215D-VZ | 9-18              | ±15                | ±166                    | ±220                      | 77             |
| AM5T-1224D-VZ | 9-18              | ±24                | ±104                    | ±100                      | 76             |
| AM5T-2405D-VZ | 18-36             | ±5                 | ±500                    | ±1000                     | 74             |
| AM5T-2409D-VZ | 18-36             | ±9                 | ±277                    | ±220                      | 76             |
| AM5T-2412D-VZ | 18-36             | ±12                | ±208                    | ±220                      | 78             |
| AM5T-2415D-VZ | 18-36             | ±15                | ±166                    | ±220                      | 78             |
| AM5T-2424D-VZ | 18-36             | ±24                | ±104                    | ±100                      | 75             |
| AM5T-4805D-VZ | 36-72             | ±5                 | ±500                    | ±1000                     | 76             |

### Models

#### Dual output (continued)

| Model            | Input Voltage (V) | Output Voltage (V) | Output Current max (mA) | Max. Capacitive load (μF) | Efficiency (%) |
|------------------|-------------------|--------------------|-------------------------|---------------------------|----------------|
| AM5T-4809D-VZ    | 36-72             | ±9                 | ±277                    | ±220                      | 78             |
| AM5T-4812D-VZ    | 36-72             | ±12                | ±208                    | ±220                      | 78             |
| AM5T-4815D-VZ    | 36-72             | ±15                | ±166                    | ±220                      | 80             |
| AM5T-4824D-VZ    | 36-72             | ±24                | ±104                    | ±100                      | 77             |
| AM5T-1205DH35-VZ | 9-18              | ±5                 | ±500                    | ±1000                     | 72             |
| AM5T-1209DH35-VZ | 9-18              | ±9                 | ±277                    | ±220                      | 76             |
| AM5T-1212DH35-VZ | 9-18              | ±12                | ±208                    | ±220                      | 77             |
| AM5T-1215DH35-VZ | 9-18              | ±15                | ±166                    | ±220                      | 77             |
| AM5T-1224DH35-VZ | 9-18              | ±24                | ±104                    | ±100                      | 76             |
| AM5T-2405DH35-VZ | 18-36             | ±5                 | ±500                    | ±1000                     | 74             |
| AM5T-2409DH35-VZ | 18-36             | ±9                 | ±277                    | ±220                      | 76             |
| AM5T-2412DH35-VZ | 18-36             | ±12                | ±208                    | ±220                      | 78             |
| AM5T-2415DH35-VZ | 18-36             | ±15                | ±166                    | ±220                      | 78             |
| AM5T-2424DH35-VZ | 18-36             | ±24                | ±104                    | ±100                      | 75             |
| AM5T-4805DH35-VZ | 36-72             | ±5                 | ±500                    | ±1000                     | 76             |
| AM5T-4809DH35-VZ | 36-72             | ±9                 | ±277                    | ±220                      | 78             |
| AM5T-4812DH35-VZ | 36-72             | ±12                | ±208                    | ±220                      | 78             |
| AM5T-4815DH35-VZ | 36-72             | ±15                | ±166                    | ±220                      | 80             |
| AM5T-4824DH35-VZ | 36-72             | ±24                | ±104                    | ±100                      | 77             |

### Input Specifications

| Parameters              | Nominal            | Typical | Maximum | Units |
|-------------------------|--------------------|---------|---------|-------|
| Voltage Range           | 12                 | 9-18    |         | VDC   |
|                         | 24                 | 18-36   |         | VDC   |
|                         | 48                 | 36-72   |         | VDC   |
| Filter                  | $\pi$ (Pi) Network |         |         |       |
| Start up time           |                    | 20      |         | ms    |
| Absolute Maximum Rating | 12 Vin             | -0.7-24 |         | VDC   |
|                         | 24 Vin             | -0.7-40 |         | VDC   |
|                         | 48 Vin             | -0.7-80 |         | VDC   |
| Peak Input Voltage time |                    |         | 100     | ms    |

### Isolation Specifications

| Parameters         | Conditions         | Typical | Rated | Units |
|--------------------|--------------------|---------|-------|-------|
| Tested I/O voltage | 60 sec             |         | 1500  | VDC   |
|                    | 60 sec, H35 models |         | 3500  | VDC   |
| Resistance         |                    | > 1000  |       | MOhm  |
| Capacitance        |                    | 60      |       | pF    |

### Output Specifications

| Parameters                | Conditions         | Typical | Maximum | Units  |
|---------------------------|--------------------|---------|---------|--------|
| Voltage accuracy          |                    | ±1      |         | %      |
| Voltage balance           | Balanced Load      | ±1      |         | %      |
| Short circuit protection  | Continuous         |         |         |        |
| Short circuit restart     | Auto Recovery      |         |         |        |
| Line voltage regulation   | HL-LL              | ±0.5    |         | %      |
| Load voltage regulation   | 25-100% Load       | ±0.5    |         | %      |
| Temperature coefficient   |                    | ±0.02   |         | %/°C   |
| Ripple & Noise (see note) | At 20MHz Bandwidth | 60      |         | mV p-p |

Note: For ripple and noise specification, a 100 μF capacitor must be placed on the output of converter.

## General Specifications

| Parameters            | Conditions                                              | Typical                                          | Maximum | Units |
|-----------------------|---------------------------------------------------------|--------------------------------------------------|---------|-------|
| Switching frequency   |                                                         | 100-400                                          |         | KHz   |
| Operating temperature | Full Load (see derating chart)                          | -40 to +85                                       |         | °C    |
| Storage temperature   |                                                         | -40 to +125                                      |         | °C    |
| Derating              | 71 to 85 °C                                             | 3.45                                             |         | %/ °C |
| Max Case temperature  |                                                         |                                                  | 100     | °C    |
| Cooling               | Free air convection                                     |                                                  |         |       |
| Humidity              |                                                         |                                                  | 95      | %     |
| Case material         | Nickel coated copper                                    |                                                  |         |       |
| Weight                |                                                         | 17                                               |         | g     |
| Dimensions(L x W x H) | Tolerance ±0.5 mm or ±0.02 inches                       | 1.25 x 0.8 x 0.4 inches 31.75 x 20.32 x 10.16 mm |         |       |
| MTBF                  | >1,000,000 hrs (MIL-HDBK -217F, Ground Benign, t=+25°C) |                                                  |         |       |

## Safety Specifications


| Parameters |                              |
|------------|------------------------------|
| Standards  | Designed to meet IEC 60950-1 |

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.


## Pin Out Specifications

| Pin | 1500 and 3500VDC |           |
|-----|------------------|-----------|
|     | Single           | Dual      |
| 2   | -V Input         | -V Input  |
| 3   | -V Input         | -V Input  |
| 9   | No pin           | Common    |
| 11  | N.C.             | -V Output |
| 14  | +V Output        | +V Output |
| 16  | -V Output        | Common    |
| 22  | +V Input         | +V Input  |
| 23  | +V Input         | +V Input  |

## Dimensions



## Derating



**NOTE:** 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to [www.aimtec.com](http://www.aimtec.com) for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at [www.aimtec.com](http://www.aimtec.com).