

8.5(H)mm, 3.0mm-travel Type Slide Switch SSSU Series


Detail

Part number	SSSU113200
Travel	3mm
Operating section directions	Horizontal
Length of operating section	6mm
Poles	1
Positions	3
Operating force	Refer to the dimensions.
Mounting method	Snap-in (t1.6)
Changeover timing	Non shorting
Soldering	Manual, Dip
Minimum order unit (pcs.)	2,500

Operating temperature range	-10? to +60?		
Rating (max.)/(min.) (Resistive load)	0.1A 30V DC/50μ A 3V DC		
Electrical performance	Contact resistance (Initial performance/After lifetime)	25m? max./65m? max.	
	Insulation resistance	100M? min. 500V DC	
	Voltage proof	500V AC for 1 minute	
Mechanical performance	Terminal strength	5N for 1 minute	
	Actuator strength	Operating direction	30N
		Pulling direction	30N, Static force
	Resistance to soldering heat	Manual soldering	350±10? , 3(+1, 0)s
Dip soldering		260±5? , 10±1s	
Durability	Operating life without load	10,000 cycles 45m? max.	
	Operating life with load (Load: as ratings)	10,000 cycles 65m? max.	
Environmental performance	Cold	-20±2? for 96h	
	Dry heat	85±2? for 96h	
	Damp heat	40±2? , 90 to 95%RH for 96h	


TOP

Dimensions



TOP


Mounting Hole Dimensions



Viewed from direction A in the dimensions.


TOP

Actuator configuration




TOP

Shape of Frame Leg



TOP

Circuit Diagram



TOP

NOTE

- Notes are common to this series/models.
- This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
 - Please place purchase orders per minimum order unit (integer).
 - Products other than those listed in the above chart are also available. Please contact us for details.
 - Please contact us for automotive use.

Inquiries about Products

For more information please contact: Products Information Center.
1-7, Yukigaya-otsukamachi, Ota-ku, Tokyo, 145-8501, Japan
Phone: +81 (3) 5499-8154