

Series AM15TW-Z

15 Watt | DC-DC Converter



FEATURES:

- Ultra Wide Input Range 4:1
- 1600 VDC Isolation
- Efficiency up to 90%
- Soft Start
- Remote On/Off Function
- No Minimum Load Required
- -40°C to +85°C Operating Temperature Range
- Short Circuit & Over Voltage Protection
- DIP 24 Package
- Low No Load Input Current

Models Single output



Model	Input Voltage (V)	Output Voltage (V)	Output Current max (mA)	Isolation (VDC)	Maximum Capacitive load (μF)	Efficiency (%)
AM15TW-2403SZ	9-36	3.3	4000	1600	4700	88
AM15TW-24051SZ	9-36	5.1	3000	1600	3300	90
AM15TW-2412SZ	9-36	12	1250	1600	600	90
AM15TW-2415SZ	9-36	15	1000	1600	400	90
AM15TW-4803SZ	18-75	3.3	4000	1600	4700	89
AM15TW-48051SZ	18-75	5.1	3000	1600	3300	89
AM15TW-4812SZ	18-75	12	1250	1600	600	90
AM15TW-4815SZ	18-75	15	1000	1600	400	90

Models Dual output

Model	Input Voltage (V)	Output Voltage (V)	Output Current max (mA)	Isolation (VDC)	Maximum Capacitive load (μF)	Efficiency (%)
AM15TW-2405DZ	9-36	±5	±1500	1600	±1500	86
AM15TW-2412DZ	9-36	±12	±625	1600	±288	89
AM15TW-2415DZ	9-36	±15	±500	1600	±200	90
AM15TW-4805DZ	18-75	±5	±1500	1600	±1500	86
AM15TW-4812DZ	18-75	±12	±625	1600	±288	89
AM15TW-4815DZ	18-75	±15	±500	1600	±200	90

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified

Input Specifications

Parameters	Nominal	Typical	Maximum	Units
Voltage range	24 48	9-36 18-75		VDC
Filter	π (Pi) Network			
Transient recovery time	Nominal Vin, 25% load step change	250		μs
Transient response deviation	Nominal Vin, 25% load step change		±3	%
Start up time	Nominal Vin and constant resistive load	20		ms
Absolute Maximum Rating	24 Vin models 48 Vin models	-0.7-50 -0.7-100		VDC
Peak Input Voltage time			1000	ms
Input reflected ripple current	With a 12μH inductance and a 47μF capacitor		20	mA p-p
Quiescent Current			15	mA
On/Off Control	ON – High (3.0 ... 12Vdc) or open circuit; OFF – Low (0 ... 1.2Vdc) or Short circuit pin1 and pin 2/3 OFF idle current: 5.0 mA typ			

Isolation Specifications

Parameters	Conditions	Typical	Rated	Units
Tested I/O voltage	60 sec		1600	VDC
Tested Case/Input and Output		1600		VDC
Resistance		>1000		MOhm
Capacitance		2000		pF

Output Specifications

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy			±1	%
Voltage balance	1 st output 25-100% load, 2 nd output 100% load		±5	%
Line voltage regulation	Single, HL-LL		±0.2	%
	Dual, HL-LL		±0.5	%
Load voltage regulation	Single, 0% Load to 100% load		±0.5	%
	Dual, 0% to 100% load, balance load		±1.0	%
Over voltage protection	Zener diode clamp, 3.3Vout	3.9		VDC
	Zener diode clamp, 5.1Vout	6.2		VDC
	Zener diode clamp, 12Vout	15		VDC
	Zener diode clamp, 15Vout	18		VDC
	Zener diode clamp, ±5Vout	±6.2		VDC
	Zener diode clamp, ±12Vout	±15		VDC
	Zener diode clamp, ±15Vout	±18		VDC
Over current protection	Full Load	150		% of Iout
Short Circuit protection	Continuous			
Short circuit restart	Auto recovery			
Ripple & Noise*	20MHz Bandwidth		60	mVp-p

* Measured with a 1μF ceramic capacitor

General Specifications

Parameters	Conditions	Typical	Maximum	Units
Switching frequency		250 to 330		KHz
Operating temperature	Full Load with derating above 60°C	-40 to +85		°C
Storage temperature		-55 to +125		°C
Max Case temperature			105	°C
Temperature coefficient		±0.02		%/°C
Derating	Above 60°C	2.5		%/°C
Cooling	Free air convection			
Humidity			95	% RH
Case material	Nickel-coated Copper			
Weight		20.0		g
Dimensions (L x W x H)	Tolerance ±0.5 mm or ±0.02 inches	1.25 x 0.8 x 0.4inches	31.8 x 20.3 x 10.2mm	
MTBF	> 410 000 hrs (MIL-HDBK -217F, Ground Benign, t=+25°C)			
Manual soldering temperature	1.5mm from case for 10sec		260	°C


Safety Specifications

Parameters	
Agency Approval	CE
Standards	Designed to meet IEC/EN/UL60950-1, 62368-1
	EN55032 Class A
	IEC61000-4-2, Perf. Criteria B
	IEC61000-4-3, Perf. Criteria A
	IEC61000-4-4, Perf. Criteria B (requires 2 external cap 330μF/100V or 1 cap 680μF/100V for parallel connection)
	IEC61000-4-5, Perf. Criteria B (requires 2 external cap 330μF/100V or 1 cap 680μF/100V for parallel connection)
	IEC61000-4-6, Perf. Criteria A
	IEC61000-4-8, Perf. Criteria A


Pin Out Specifications

Pin	Single	Dual
1	Remote On/Off	Remote On/Off
2	-V Input	-V Input
3	-V Input	-V Input
9	No Pin	Common
11	N.C	-V Output
14	+V Output	+V Output
16	-V Output	Common
22	+V Input	+V Input
23	+V Input	+V Input

Dimensions



Derating



NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity < 75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other than the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.